



## TPC11FGPC004 Product Details



**TPC11FGPC004**

TE Internal Number: 1825098-5



### Pushbutton Switches

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Switch
- Not Tactile
- Single Pole - Double Throw Configuration (Pole-Throw)
- Contact Rating = 0.4VA
- Operating Function = Momentary

[View all Features](#)

### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)



[Request Sample](#)



[Find Similar Products](#)



[Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [PUSHBUTTON SWITCH, TPC SERIES](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Product Type = Switch
- Tactile = No
- Configuration (Pole-Throw) = Single Pole - Double Throw
- [Series](#) = TPC
- Mount Angle = Vertical
- Termination Type = Printed Circuit
- Actuator Style = Round

#### Electrical Characteristics:

- Contact Rating = 0.4VA

#### Body Features:

- Mount Style = Through-Hole
- Actuator Length (mm [in]) = 3.48 [0.137]
- Actuator Profile = Extended
- Actuator Color = Black
- Bushing Diameter = 10/48
- Case Material = Polyester
- Actuator Material = Polyamide

#### Contact Features:

- Contact Plating = Gold over Nickel

#### Housing Features:

- Process Sealed = No
- Low Profile = No
- Bushing Style = Threaded

#### Configuration Features:

- Operating Function = Momentary
- Ganged = No
- ESD Grounding Terminal = Without
- Actuator Force (g [oz]) = 260.00 [9.178]
- Number of Actuators = Single
- Illuminated = No
- Dust Proof = No
- Support Bracket = Without
- Snap Action = Without

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Conditions for Usage:

- Temperature Rating = High

#### Packaging Features:

- Packaging Method = Loose Piece

#### Other:

- Brand = Alcoswitch

### Corporate Information

[Who We Are](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

### Quick Links

[Check Distributor Inventory](#)

[Cross Reference](#)

[Find Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

### Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Search Knowledge Base](#)

[Manage your Account](#)

### Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

