

Test adapter - PAI-4-FIX VT

3032761

<https://www.phoenixcontact.com/us/products/3032761>



Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



Test adapter, Touch proof against unintentional direct contact according to DIN EN 50274 when plugged in, for 4 mm test plug and terminal blocks with 4.2 mm ... 8.2 mm pitch, color: violet

Your advantages

- Make contact and latch securely to any point in the function shaft
- Test adapter for accommodating safety test plugs with a 4 mm diameter

Test adapter - PAI-4-FIX VT

3032761

<https://www.phoenixcontact.com/us/products/3032761>



Commercial Data

Item number	3032761
Packing unit	1 pc
Minimum order quantity	10 pc
Sales Key	B02
Product Key	BE2Z3X
Catalog Page	Page 116 (C-1-2019)
GTIN	4046356280341
Weight per Piece (including packing)	2.45 g
Weight per Piece (excluding packing)	2.39 g
Customs tariff number	85366990
Country of origin	PL

Test adapter - PAI-4-FIX VT

3032761

<https://www.phoenixcontact.com/us/products/3032761>



Technical Data

Notes

General	Touch proof against unintentional direct contact according to DIN EN 50274 when plugged in
General	Do not plug in while the power is connected
General	Latching testing accessories, therefore only suitable for being plugged in once

Product properties

Product type	Test socket
Number of positions	1

Electrical properties

Maximum load current	10 A
Max. voltage	250 V

Connection data

Maximum load current	10 A
----------------------	------

Dimensions

Width	5.8 mm
Height	51.5 mm
Length	5.8 mm
Diameter	5.8 mm
Pin diameter	2.4 mm

Material specifications

Color	violet
Material	PA
Flammability rating according to UL 94	V0
Insulating material	PA

Connector

Insertion/withdrawal cycles	1
-----------------------------	---

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Test adapter - PAI-4-FIX VT

3032761

<https://www.phoenixcontact.com/us/products/3032761>



Approvals

EN EAC

Test adapter - PAI-4-FIX VT

3032761

<https://www.phoenixcontact.com/us/products/3032761>



Classifications

ECLASS

ECLASS-9.0	27440313
ECLASS-10.0.1	27440313
ECLASS-11.0	27141148

ETIM

ETIM 8.0	EC002555
----------	----------

UNSPSC

UNSPSC 21.0	20122000
-------------	----------

Test adapter - PAI-4-FIX VT

3032761

<https://www.phoenixcontact.com/us/products/3032761>



Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Phoenix Contact 2022 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com