

Specifications



Photo is representative



Eaton 187069

Eaton Moeller® series M30 Key-operated actuator, Flat Front, momentary, 3 positions, Key withdrawable: 0, Metal bezel

General specifications

PRODUCT NAME	Eaton Moeller® series M30 Key-operated actuator
CATALOG NUMBER	187069
MODEL CODE	M30C-FWS3
EAN	4015081821303
PRODUCT LENGTH/DEPTH	36 mm
PRODUCT HEIGHT	67 mm
PRODUCT WIDTH	46 mm
PRODUCT WEIGHT	0.06 kg

CERTIFICATIONS

IEC/EN 60947
VDE 0660
CSA file No. 012528
CSA Class No.: 3211-03
DNV
UL File No.: E29184
GL
IEC/EN 60947-5
UL 508
CSA-C22.2 No. 14-05
CSA-C22.2 No. 94-91
CE marking
UL Category Control No.:
NKCR
UL Listed
CSA certified

Product specifications

TYPE	Key-operated button
ACCESSORIES	1 key included with supplied equipment.
ACTUATOR COLOR	Black
ACTUATOR FUNCTION	Key withdrawable in position 0 Momentary Spring-return
10.10 TEMPERATURE RISE	Not applicable.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Please enquire
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.

Resources

CATALOGS

[eaton-rmq-titan-brochure-br047004en-en-us.pdf](#)

[Flip catalog - Product Range Catalog - Command and indication](#)

[eaton-pushbuttons-signal-towers-sensors-assortment-overview-catalog-ca047003en-en-us.pdf](#)

DECLARATIONS OF CONFORMITY

[DA-DC-00004157.pdf](#)

[DA-DC-00004135.pdf](#)

[eaton-operating-m30-key-operated-actuator-dimensions.eps](#)

[eaton-operating-m30-dimensions-005.eps](#)

[eaton-operating-m30-dimensions-006.eps](#)

DRAWINGS

[eaton-operating-m30-dimensions-004.eps](#)

[eaton-operating-m30-key-operated-actuator-3d-drawing.eps](#)

[eaton-general-m22-symbol.eps](#)

[eaton-general-approval-m22-symbol.eps](#)

ECAD MODEL

[ETN.187069.edz](#)

INSTALLATION INSTRUCTIONS

[eaton-operating-devices-m30-rmq-titan-flat-front-instruction-leaflet-il047019zu.pdf](#)

INSTALLATION VIDEOS

[RMQ Flat Design](#)

MCAD MODEL

[DA-CS-schluesseltaste_ms_flatfront](#)

[DA-CD-schluesseltaste_ms_flatfront](#)

MULTIMEDIA

[easyE4 SmartWire-DT module with Remote Touch Display and RMQ multi color indicator](#)

[MCI Multicolor Light Indicator M22 with SmartWire-DT](#)

[RMQ small E-Stop emergency-stop button](#)

[MCI MultiColor Light Indicator RMQ compact solution](#)

[eaton-rmq-small-e-stop-flyer-fl047006en-en-us.pdf](#)

SALES NOTES

[eaton-rmq-flat-enclosure-flyer-fl047003en-en-us.pdf](#)

10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Plunger bridge for the middle contact Front ring
OPERATING FREQUENCY	100 Operations/h
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
CONNECTION TO SMARTWIRE-DT	With SWD-RMQ connections Yes
ACTUATOR TYPE	Key
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	0 W
FORCE FOR POSITIVE OPENING - MIN	0 N
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	0 W
OPENING DIAMETER	30 mm
OPENING HEIGHT	0 mm
OPERATING TORQUE	0.5 Nm
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	0 A
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	0 W
SWITCHING ANGLE	40 °
WIDTH OPENING	0 mm
BEZEL COLOR	Titanium
SHOCK RESISTANCE	Mechanical, According to IEC/EN 60068-2-27 15 g, Mechanical, According

[eaton-control circuit-devices
rmq-titan-fl144090en-en-us.pdf](#)

[eaton-rmq-mci-multi-color-light-indicator-flyer-fl047005en-en-us.pdf](#)

SYSTEM OVERVIEW

[Pilot devices - selection aid](#)

	to IEC/EN 60068-2-27, Sinusoidal shock 11 ms
BEZEL MATERIAL	Metal
DESIGN	Key operation lock mechanism
	Flat front
MOUNTING POSITION	As required
OVERVOLTAGE CATEGORY	III
DEGREE OF PROTECTION	NEMA 4X, 13
DEGREE OF PROTECTION (FRONT SIDE)	IP64
FUNCTIONS	Stay-put/spring-return function, can be changed with coding parts M22-XC-Y
INDICATOR COLOR	Other
LENS TYPE	Round
LIFESPAN, MECHANICAL	100,000 Operations
NUMBER OF SWITCH POSITIONS	3
SIZE	Front dimensions: Ø 36 mm
PRODUCT CATEGORY	RMQ-Titan

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.