

## DSUB SV MA SSDP ANG73-254 09P PL2GCM3



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 09 65 162 6811                                                                |
| Specification      | DSUB SV MA SSDP ANG73-254 09P<br>PL2GCM3                                      |
| HARTING eCatalogue | <a href="https://harting.com/09651626811">https://harting.com/09651626811</a> |

### Identification

|                            |                   |
|----------------------------|-------------------|
| Category                   | Connectors        |
| Series                     | D-Sub             |
| Identification             | Standard          |
| Element                    | Connector         |
| Description of the contact | Stamped<br>Angled |

### Version

|                    |                              |
|--------------------|------------------------------|
| Termination method | Wave soldering termination   |
| Gender             | Male                         |
| Size               | D-Sub 1                      |
| Connection type    | Motherboard to daughtercard  |
| Number of contacts | 9                            |
| further contacts   | With grounding pin           |
| Termination length | 2.9 mm                       |
| PCB fixing         | With board locks             |
| Locking type       | Fixing flange with thread M3 |

### Technical characteristics

|                                    |         |
|------------------------------------|---------|
| Distance between rows              | 2.54 mm |
| Contact spacing (termination side) | 2.74 mm |
| Rated current                      | 6.5 A   |
| Clearance distance                 | ≥1 mm   |



Pushing Performance  
 Since 1945

## Technical characteristics

|                                  |                             |
|----------------------------------|-----------------------------|
| Creepage distance                | ≥1 mm                       |
| Insulation resistance            | >10 <sup>10</sup> Ω         |
| Contact resistance               | ≤10 mΩ                      |
| Tightening torque                | ≤0.6 Nm Female screw lock   |
| Limiting temperature             | -55 ... +125 °C             |
| Insertion force                  | ≤30 N                       |
| Withdrawal force                 | ≥3.3 N<br>≤20 N             |
| Performance level                | 2<br>acc. to CECC 75301-802 |
| Mating cycles                    | ≥250                        |
| Test voltage U <sub>r.m.s.</sub> | 1 kV                        |
| Isolation group                  | IIIa (175 ≤ CTI < 400)      |
| PCB thickness                    | ≥1.6 mm                     |
| Installation height              | 7.3 mm                      |
| Hot plugging                     | No                          |

## Material properties

|                                           |                                                                       |
|-------------------------------------------|-----------------------------------------------------------------------|
| Material (insert)                         | Thermoplastic resin, glass-fibre filled (PBTP)<br>Shell: Plated steel |
| Colour (insert)                           | Black                                                                 |
| Material (contacts)                       | Copper alloy                                                          |
| Surface (contacts)                        | Noble metal over Ni                                                   |
| Material flammability class acc. to UL 94 | V-0                                                                   |
| RoHS                                      | compliant                                                             |
| ELV status                                | compliant                                                             |
| China RoHS                                | e                                                                     |
| REACH Annex XVII substances               | Not contained                                                         |
| REACH ANNEX XIV substances                | Not contained                                                         |
| REACH SVHC substances                     | Not contained                                                         |
| California Proposition 65 substances      | Yes                                                                   |
| California Proposition 65 substances      | Lead<br>Nickel                                                        |
| Fire protection on railway vehicles       | EN 45545-2 (2020-08)                                                  |



**Pushing Performance**  
Since 1945

## Material properties

|                                    |     |
|------------------------------------|-----|
| Requirement set with Hazard Levels | R26 |
|------------------------------------|-----|

## Specifications and approvals

|                |                       |
|----------------|-----------------------|
| Specifications | DIN 41652             |
| UL / CSA       | UL 1977 ECBT2.E102079 |

## Commercial data

|                                |                        |
|--------------------------------|------------------------|
| Packaging size                 | 100                    |
| Net weight                     | 6.38 g                 |
| Country of origin              | Romania                |
| European customs tariff number | 85366990               |
| GTIN                           | 5713140077119          |
| eCl@ss                         | 27440214 D-Sub coupler |
| ETIM                           | EC001136               |
| UNSPSC 24.0                    | 39121469               |