

Part Number: 2944778301

44 PC BEAD

Explanation of Part Numbers:

- Digits 1 & 2 = Product Class
- Digits 3 & 4 = Material Grade
- Last digit 1 = Standard Wire Length 2.4 mm (0.095") Minimum, 2 = Wire Length 3.1 mm (0.122) Minimum

Multiple single turn or multi-turn printed circuit EMI suppression beads are available in two Fair-Rite materials. The broadband 44 material and in the high frequency 52 material grade.

Wires are oxygen free high conductivity copper with 100% matte tin plating over a nickel undercoating. Wires on top of the beads are covered with a layer of epoxy.


Recommended operating and storage temperature for the PC Beads is -55 °C to +125 °C.

Recommended Soldering Profile

PC Beads can be supplied with lower component heights "C". Also, the wire length "F" can be modified to specific requirements.

Weight: 6 (g)

Dim	mm	mm tol	nominal inch	inch misc.
A	11.2	-0.50	0.431	—
B	11.2	-0.50	0.431	—
C	11.8	Max	0.464	Max
D	2.54	±0.10	0.1	—
E	7.6	±0.20	0.299	—
F	2.79	±0.25	0.110	—
G	0.65	—	0	22 AWG



Typical Multi
Turn Printed
Circuit Board
Layout



Figure 3A:
4 Turn turn winding
for parts in Fig 3.



Figure 3B:
2 x 2 Turn winding
for parts in Fig 3.

Chart Legend


+ Test frequency


Typical Impedance (Ω)	
10 MHz	142
25 MHz ⁺	224
100 MHz ⁺	372
250 MHz	402

PC Beads are controlled for impedance only. Minimum impedance values are specified for the + marked frequencies. The minimum impedance is typically the listed impedance less 20%.

The PC Beads in 44 material are measured on the E4990A Impedance Analyzer. The 52 PC Beads are tested for impedance on the E4991A / HP4291B Impedance Analyzer.

Typical Impedance (Ω)	
10 MHz	142
25 MHz ⁺	219
100 MHz ⁺	338
250 MHz	335





[CSV Download](#)

Fair-Rite Products Corp. • One Commercial Row, Wallkill, New York 12589-0288

888-324-7748 • 845-895-2055 • Fax: 845-895-2629 • ferrites@fair-rite.com • www.fair-rite.com