



B




B



ISO VIEW



JACK PIN NUMBERS




SEE DETAIL
JACK PIN NUMBERS

Ø.066 [1.68](2)
⊕ Ø.006 [0.15]

.225
[5.72]

Ø.125-.128 (2)
[3.18-3.25]
⊕ Ø.006 [0.15]




COMPONENT SIDE

PCB RECOMMENDED HOLE LAYOUT
SEEN FROM COMPONENT SIDE

ALL CENTERLINE DIMENSIONS ARE BASIC

| DATE | REV. | ECN | APP'D BY |
|----------|------|-------|----------|
| 2-9-16 | C5 | 10531 | TRM |
| 10-10-17 | C6 | 11119 | TRM |
| | | | |
| | | | |



PCB PIN NUMBERS

- NOTES:
- CONNECTOR MATERIALS:
HOUSING: THERMOPLASTIC UL94 V-0
CONTACTS/SHIELD: COPPER ALLOY
SHIELD PLATING: TIN
CONTACT PLATING: SELECTIVE PLATING IN CONTACT AREA
SEE CHART FOR DETAILS.
 - PRODUCT DESIGNED FOR CATEGORY 6 APPLICATIONS
 - DIMENSIONS AND TOLERANCES COMPLY WITH TIA-1096 STANDARD.
 - REFERENCE PRODUCT SPECIFICATION PR026-01

50 MICRO-INCHES [1.27um] Au OR
5 MICRO-INCHES [0.13um] Au OVER
30 MICRO-INCHES [0.76um] PdNi


CONTACT PLATING
IN MATING AREA

SS-60000-008

PART NUMBER



A

A



RoHS



| | | | | | |
|---|--|--|--|--|---------|
| THIRD ANGLE PROJECTION  | |  stewart CONNECTOR a bel group | | 11118 Susquehanna Trail South Glen Rock, PA 17327-9199 (717) 235-7512 http://www.stewartconnector.com | |
| DO NOT SCALE DRAWING | | CATEGORY 6 SHIELDED VERTICAL JACK | | | |
| DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE | | | | | |
| DIMENSIONS: INCHES [METRIC] | | THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF STEWART CONNECTOR AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT PRIOR WRITTEN CONSENT OF STEWART CONNECTOR. ONE OR MORE U.S. PATENTS MAY APPLY TO THIS PRODUCT. FOR DETAILS, PLEASE VISIT: HTTP://BELFUSE.COM/STEWART/STEWART_PATENTS/ | | DRN BY: | DATE |
| UNLESS OTHERWISE SPECIFIED TOLERANCES ARE $\pm .005$ [0.13] ANGLES ARE $\pm 1^\circ$ | | | | JRC | 6-18-02 |
| SHEET NO. | | | | APPD BY: | DATE |
| 1 OF 1 | | | | DHG | 6-18-02 |
| | | DWG. NO. | | REV. | |
| | | CT6000008 | | C6 | |