



Part Number : [503728100](#)

Product Description : 2.00mm Pitch, Micro-Latch Female Crimp Terminal, Tin (Sn) Plating, 26-22 AWG, Bag

Series Number : 50372

Status : Not Recommended For New Design

Product Category : Crimp Terminals

Packaging Alternative : [503728000](#) (Reel)



Documents and Resources

Drawings

[503728100 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[2166940000-AS-000.pdf](#)

[510900001-000.pdf](#)

[SPK-50372-001-001.pdf](#)

[510650000-PS-000.pdf](#)

[510651000-PS-000.pdf](#)

[PS-51089-001-001.pdf](#)

[PS-51089-005-001.pdf](#)

[PS-51090-004-001.pdf](#)

[PS-51090-005-001.pdf](#)

[PS-51090-009-001.pdf](#)

[PS-51090-016-001.pdf](#)

[PS-51090-017-001.pdf](#)

[PS-51160-001-001.pdf](#)

[PS-51160-006-001.pdf](#)

[PS-52968-006-001.pdf](#)

[PS-52968-007-001.pdf](#)

[PS-53717-002-001.pdf](#)

[PS-54111-002-001.pdf](#)


[PS-55533-004-001.pdf](#)

Tooling Specifications

[CS-50372-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Not Recommended For New Design
--------	--------------------------------

Category	Crimp Terminals
Series	50372
Description	2.00mm Pitch, Micro-Latch Female Crimp Terminal, Tin (Sn) Plating, 26-22 AWG, Bag
Application	Signal, Wire-to-Board
Product Name	Mi II, Micro-Latch
UPC	800753352704

Electrical

Current - Maximum per Contact	2.5A
Voltage - Maximum	250V AC (RMS)/DC

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	26.800/mg
Packaging Type	Bag
Plating min - Mating	0.900µm
Plating min - Termination	0.900µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.40mm max.
Wire Size (AWG)	22, 24, 26
Wire Size mm ²	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
Micro-Latch Single Row Receptacle Housings	<u>51065</u>
Mi II Single Row Crimp Housings	<u>51089</u>
Mi II Single Row Crimp Housings	<u>51090</u>

Application Tooling

Global

Description	Part Number
Extraction Tool for Micro-Fit Terminals	<u>11030043</u>
PremiumGrade Hand Crimp Tool for Micro-Latch, DuraClik, and Servo Motor Encoder Female Terminals, 26-22 AWG	<u>638235100</u>

Japan

Description	Part Number
Extraction Tool	<u>573216000</u>

This document was generated on Apr 29, 2026