Downloaded from Arrow.com.

ITEM NO	QTY	SIZE	NUMBER	NAME	REMARKS
11	4	A	313036-4	LABEL GREEN	
10	1	A	2304052-1	LOCATOR	
9	2	—	2-210015-5	SCREW	
8	1	A	5-21028-1	PIN	
7	1	A	3-305833-1	SPACER	
6	1	A	V-305731-5	ANVIL	
5	1	A	V-305130-5	INDENTER	
4	1	A	300389	PIN-RETAINING	
3	2	—	21045-6	RING-RETAINING	
2	2	A	300388	PIN-RETAINING	
1	4	—	21045 3	RING-RETAINING	

REQUIRED PER ASSEMBLY

LTR	REVISION RECORD	DATE	APPD
K	REVISED		
J	REVISED		
H	REVISED		
A	RELEASED		

DESCRIPTION


A" DIM.	
209	.215
60	NO GO

ENLARGED VIEW OF CRIMP

A" DIM.

For replacement of parts other than listed, Tool should be returned to our Factory to insure proper Certi-Crimp adjustment.

Gage dimensions apply when tool is bottomed but not under pressure.



WIRE RANGE	18-8	HEAVY HEAD HAND TOOL ASSY	
AREA	—	SCALE NAME	SHEET 1 OF 1
CLASS	—	TYPE "C" ECV	
DR	C. Mayes 6-16-69	FIRST USED	
CHK	Ray L. 8-5-69	CPD. P.	
APP	Ray L. 8-5-69		

M	C	NO 69335	REV K

AMP INCORPORATED HARRISBURG, PENNA.

UNLESS OTHERWISE SPECIFIED: REMOVE BURRS, BREAK SHARP EDGES 1/64 R. MAX. FRACTIONS: ± 1/64 ANGLES: ± 0° 30' DECIMALS: .000 = ± .005 .0000 = ± .0005

AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING. ©1969 BY AMP INCORPORATED. ALL RIGHTS RESERVED.

CUSTOMER CERT REFERENCE ONLY

DIMENSIONS IN INCHES. DO NOT SCALE PRINT.

AMP 1256 REV 7/69

NUMBER 69335