

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

TYPE 1

Surface mounting

4X M3 THREAD
4X M3 螺纹孔

4XØ4.5

2X M6 THREAD
2X M6 螺纹孔

56

32

27

77.5

103

116

129.5

21.9

19

TYPE 2

Surface mounting

4X M3 THREAD
4X M3 螺纹孔

2X M6 THREAD
2X M6 螺纹孔

60

27

77.5

116

129.5

21.9

19

112.5

103

91

82

40

35

32

FOR EMC FEATURES,
CONDUCTIVE SURFACE

4X R7

Panel Cut Out Dimension For TYPE 1, Only for Reference
面板开口尺寸, 仅供参考

112.5

91

82

43

40

35

FOR EMC FEATURES,
CONDUCTIVE SURFACE

4X R7

Panel Cut Out Dimension For TYPE 2, Only for Reference
面板开口尺寸, 仅供参考

OBsolete

T1932160001-009

H16BPR-AGCT-EMC-C

H16BPR HOUSING,CENTER LOCKING,BULKHEAD FLANGE MOUNTED,POWDER COATED,BLACK
H16BPR中部锁定面板型开孔下壳 黑色

TYPE 2
类型2

T1932162000-009

H16BPR-AGC-EMC-C

H16BPR HOUSING,CENTER LOCKING,BULKHEAD MOUNTED,POWDER COATED,GREY
H16BPR中部锁定开孔下壳 灰色

TYPE 1
类型1

T1932161000-009

H16BPR-AGC-EMC-C

H16BPR HOUSING,CENTER LOCKING,BULKHEAD MOUNTED,POWDER COATED,SILVER WHITE
H16BPR中部锁定开孔下壳 银白色

TYPE 1
类型1

T1932160000-009

H16BPR-AGC-EMC-C

H16BPR HOUSING,CENTER LOCKING,BULKHEAD MOUNTED,POWDER COATED,BLACK
H16BPR中部锁定开孔下壳 黑色

TYPE
类型

PART NUMBER
料号

DESCRIPTION
描述

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
-

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC
ANGLES
FINISH

±
±
±
±
±
±
±

DAVID.WANG
CHRIS.WANG

08OCT2016
08OCT2016

PRODUCT SPEC
108-137191
APPLICATION SPEC
114-137191

WEIGHT
-

DAVID.WANG
CHRIS.WANG

08OCT2016
08OCT2016

NAME
H16BPR-AGC/AGCT-EMC-C

SIZE
A1

CAGE CODE
-

DRAWING NO
T193216XXXXX09

RESTRICTED TO
-

Customer Drawing

SCALE
1:1

SHEET
1

OF
1

REV
B1

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
A		INITIAL RELEASE	08OCT2016	DW	CW
B		ECR-20-016312	04JUN2021	BS	CW
B1		ECR-24-214773	08AUG2024	SC	CW

NOTES:

1. TECHNICAL CHARACTERISTICS:
HOUSING MATERIAL: DIE CAST ALUMINIUM ALLOY
SURFACE : SEE TABLE
DEGREE OF PROTECTION: IP68 (MATED)

注释

1. 技术参数:
壳体材料: 铝合金
表面处理: 见表格
防护等级: IP68 (配合)

4805 (3/13)

Downloaded from Arrow.com