



Part Number : [1200860464](#)
Product Description : Nano-Change (M8)
Single-Ended Cordset, 3 Poles, A-Coded,
Female (90°) to Pigtail, with PNP LED Sensors,
0.34mm² PUR/PVC Cable, 5.0m (16.40') Length
Series Number : 120086
Status : Active
Product Category : Circular Industrial
Cordsets
Engineering Number : 4030P1P03M050




Documents & Resources

Drawings
[1200860464_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead... per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120086
Description	Nano-Change (M8) Single-Ended Cordset, 3 Poles, A-Coded, Female (90°) to Pigtail, with PNP LED Sensors, 0.34mm ² PUR/PVC Cable, 5.0m (16.40') Length
IP Rating	IP67
Product Name	Nano-Change (M8)
Type	Single Ended
UPC	78172553796

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	30V AC/DC

Physical

Cable Diameter	4.32mm (.170")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black
Connector End A	Nano-Change (M8)
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	A-Coded
LED Indicator	PNP Sensors
Material - Cable Jacket	PUR/PVC
Material - Connector Body	PUR
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass

Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	154.640/g
Orientation	90° to Pigtail
Poles	3
Temperature Range - Operating	-30° TO +80°C
Wire/Cable Type	E152210
Wire Size (AWG)	N/A

This document was generated on Apr 22, 2025