




PRODUCT NUMBER	PITCH
TJxx71x400J0G	5.00 mm



Corresponding poles
for the handle

product	handle
2P-4P	2P
5P-9P	5P
10P-15P	8P
16P-24P	12P

N = Number of poles
Dim A = N x 5.0
Dim B = (N-1) x 5.0

	Dim A	Dim B
2-6p	±0.20	±0.15
7-12p	±0.25	±0.20
13-18p	±0.30	±0.25
19-24p	±0.40	±0.30

Material

- Item ① Clamp: Brass(CuZn) Ni plated
- Item ② Terminal screw: Steel Zinc plating "-" slot type
- Item ③ Female contact: High conductivity copper, Tin plated
- Item ④ Terminal (Cover): Thermoplastic (UL94V-0)
- Item ⑤ Terminal (Body): Thermoplastic (UL94V-0)
- Item ⑥ Handle: Thermoplastic (UL94V-0)

Electrical cULus/VDE/TUV

- Voltage rating: 300V/300V/300V
- Current rating: 20A/20A/20A
- Wire range:
- Solid wire(AWG): 12-24
- Stranded wire(AWG): 12-24
- Torque: 5Lb-In/0.5Nm/0.56Nm
- Screw: M3
- Wire strip length: 7-8mm
- Withstanding Voltage: 1.6KV/2.5KV/2.5KV
- Operating temperature: -40°C to +115°C
- Safety Approval: cULus VDE TÜV

PART NO.: TJ xx 71 x 4 00J0 G

No. of poles	Body Color	RoHS compliant
02 2 poles	0 Black (RAL9005)	(lead<4%)
03 3 poles	2 Red (RAL3001/D)	In copper Alloy
...	3 Orange(RAL2011/P)	
24 24 poles	4 Yellow(RAL1018/A)	
	5 Green(RAL6018/T)	
	6 Blue (RAL5015/A)	
	8 Grey(RAL7035/D)	
	9 White(RAL1102)	
	C Green(RAL6018/U)	

mat'l. code				surface	tolerance	projection	product family		
				ASME Y14.5	ASME Y14.5		TERMINAL BLOCK		
ltr	ecn	no	dr	date	tolerances unless otherwise specified		 title TERMINAL BLOCK PLUGGABLE PLU, WITH HANDLE scale 		
					angles	X.±0.5			
						X.X±0.3			
					X*±1°	X.XX±0.1	sheet 1 of 1 size		
					dr	HANKE FENG 032614	TJxx71x400J0G		
					enr	HANKE FENG 032614	A4		
					chr	SHI JUN 032614	CUSTOMER Drawing		
					appd	SHI JUN 032614			
sheet index	revision	A							
	sheet	1							