



PRODUCT NUMBER	PITCH
VPxx65x500J0G	10.16 mm



PART NO.: VP xx 6 5 x 5 00J0 G



N = Number of poles
Dim L=N×10.16
Dim B=(N-1)×10.16

Poles	Tolerance
2-4p	±0.15
5-8p	±0.25
9-12p	±0.35

End Stackable
No. of poles
02 2 poles
03 3 poles
...
12 12 poles

Body Color
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)
9 White(RAL1102)
C Green(RAL6018/U)

RoHS compliant
(lead<4%)
In copper Alloy



Material:

- Item①Terminal housing :Thermoplastic (UL 94V-0)
- Item②Clamp : Steel stamping , Zinc plated
- Item③Solder pin1: Copper , Tin plated
- Item④Solder pin2 : Copper , Tin plated
- Item⑤Terminal screw: Steel Zinc plating"- "slot type

- Electrical cULus IEC
- Voltage rating : 300V 250V
 - Current rating : 65A 57A
 - Wire range :
 - Solid wire (AWG) : 6-20 / 0.5-16mm²
 - Stranded wire (AWG) : 6-20 / 0.5-16mm²
 - Torque : 19 Lb-In / 1.2 N.m
 - Screw : M4.5
 - Wire strip length : 10-11mm
 - Withstanding voltage : 1.6KV / 4KV
 - Operating temperature : -40°C+115°C
 - Soldering temperature : 260°C+5°C/5 Sec
 - Safety Approval : cULus

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family	
ltr	ecn	no	dr	date	tolerances unless otherwise specified	MM	TERMINAL BLOCK	
					angles X±0.5		title	
					X.X±0.3		TERMINAL BLOCK	
					X*±1"		RISING CLAMP,DOUBLE PARALLEL TAIL TYPE	
					dr EVIN ZHONG 041414	scale	dwg no	
					enr EVIN ZHONG 041414		sheet 1 of 1 size	
					chr HANKE FENG 041414		VPxx65x500J0G	
					appd SHI JUN 041414		type	
							CUSTOMER Drawing	
sheet index	revision	A						
	sheet	1						