


Datasheet

LL04CR-CECxxL06

Available Distribution




Dimensions

Part Number	Height	LxW
LL04CR-CEC09L06	9.96	50x50
LL04CR-CEC25L06	8.5	
LL04CR-CEC50L06	8.5	

*All dimensions are in millimeters.


LED



Recommand Applications



Packaging Details (SPQ)



General Information




- Lens Material PMMA 8N
- Operating Temperature -40°C~+70°C
- UL Flammability HB @1.5mm
- UL RTI Elec 90°C @1.5mm
- Light Transmission Rate 400nm~900nm > 90%
- ☑ If necessary, Clean lenses with mild soap, water and soft cloth.
- ⚠ Never use any commercial cleaning solvents on lenses, like alcohol.
- 🧤 Please handle or install lenses with wearing gloves, skin oils may damage lens or its optical characteristic.

Mechanical Specification

*All dimensions are in millimeters.


Lens Dimension

LL04CR-CEC09L06



Lens Dimension


LL04CR-CECxxL06 (25°/50°)



Assembly Instruction

Fixing Method


Part No LL04CR-CEC09L06



Assembly Instruction

Fixing Method


Part No LL04CR-CECxxL06 (25°/50°)



Assembly Instruction

Fixing Method


Part No LL04CR-CEC09L06




Assembly Instruction

Fixing Method

Part No LL04CR-CECxxL06 (25°/50°)



Photometric Distribution



Details by LED

Part No	Accessories	LED Package Size	LED
LL04CR-CECxxL06	-	3535 / 5050	 CREE XHP35-HD  CREE XPE2  CREE XP-G3  CREE XPL-HD  CREE XPL-HI  CREE XT-E  NICHIA NVSxx19B  SAMSUNG LH351C  SAMSUNG LH351D  SAMSUNG LH508A+

LED	Part No	FWHM	cd / lm	IES
 CREE XHP35-HD	LL04CR-CEC09L06	19°	3.8	
	LL04CR-CEC25L06	27°	2.4	
	LL04CR-CEC50L06	51°	1.0	
 CREE XPE2	LL04CR-CEC09L06	8°	17.9	
	LL04CR-CEC25L06	21°	4.9	
	LL04CR-CEC50L06	-	-	-
 CREE XP-G3	LL04CR-CEC09L06	14°	6.8	
	LL04CR-CEC25L06	24°	3.1	
	LL04CR-CEC50L06	45°	1.3	
 CREE XPL-HD	LL04CR-CEC09L06	18°	5.3	
	LL04CR-CEC25L06	24°	3.1	
	LL04CR-CEC50L06	44°	1.3	
 CREE XPL-HI	LL04CR-CEC09L06	11°	10.5	
	LL04CR-CEC25L06	21°	4.2	
	LL04CR-CEC50L06	-	-	-
 CREE XT-E	LL04CR-CEC09L06	10°	11.9	
	LL04CR-CEC25L06	21°	4.2	
	LL04CR-CEC50L06	-	-	-
 NICHIA NVSxx19B	LL04CR-CEC09L06	15°	6.5	
	LL04CR-CEC25L06	24°	3.1	
	LL04CR-CEC50L06	-	-	-
 SAMSUNG LH351C	LL04CR-CEC09L06	14°	7.9	
	LL04CR-CEC25L06	22°	3.9	
	LL04CR-CEC50L06	-	-	-
 SAMSUNG LH351D	LL04CR-CEC09L06	19°	4.8	
	LL04CR-CEC25L06	25°	3.1	
	LL04CR-CEC50L06	-	-	-
 SAMSUNG LH508A+	LL04CR-CEC09L06	-	-	-
	LL04CR-CEC25L06	28°	1.7	
	LL04CR-CEC50L06	36°	1.5	

Product Nomenclature

Ledlink Led Type Lens Angle
LL 04 CR- CEC 09 L06
Lens Dot Number Serial Number Type of Material

Ledlink Optics, Inc

Taiwan HQ

15F, No.655,Bannan Rd., Chung-Ho Dist.,
New Taipei City, Taiwan 235

Ledlink Optics (Dongguan) Co., Ltd

Dongguan Factory

No.5, TianKeng Industrial Dist., HengLi Town, DongGuan City,
GuangDong Province, China 523478

Ledlink Optics (Yangzhou) Co., Ltd

Yangzhou Factory

No.180, LinJiang Rd., YangZhou City, Jiangsu Province, China 225009

www.ledlink-optics.com

service@ledlink-optics.com

