

San Ace

DC

DC Fan

150mm
San Ace 150

"San Ace 150" GV Type

General specifications

Material	Frame, Impeller:Plastics
Life Expectancy	Varies for each model (Survival rate: 90% at 60°C, rated voltage, and continuously run in a free air state)
Motor Protection System	Current blocking function (with reverse polarity protection)
Dielectric Strength	50/60 Hz, 500VAC, 1 minute (between lead conductor and frame)
Noise Measurement Method	Measured at 1m from the air inlet
Operating Temperature Range	Varies for each model (Non-condensing)
Lead Wire	⊕red, ⊕black
Mass	450g




50mm thick Specifications


Model No.	Rated Voltage (V)	Operating Voltage Range (V)	Rated Current (A)	Rated Input (W)	Rated Speed (min ⁻¹)	Air Flow (m ³ /min) (CFM)		Static Pressure (Pa) (inchH ₂ O)	Noise (dB [A])	Operating Temperature Range (°C)	Life Expectancy (h)	
9GV1512H502(5021)	12	10.2~13.8	2.9	34.8	3,900	8.54	300	210	0.84	61	-10~+70	40,000
9GV1512M502(5021)			1.2	14.4	3,000	6.35	224	132	0.53	53		

The numbers in () represent ribless models.


Air Flow and Static Pressure Characteristics




9GV1512H502(5021)




9GV1512M502(5021)

Dimensions (unit : mm)**Reference dimension of mounting holes and vent opening (unit : mm)**

Air outlet side



Air inlet side



150mm

Notice

- The products shown in the catalog are subject to Japanese Export Control Law. Diversion contrary to the law of exporting country is prohibited.
- To protect against electrolytic corrosion that may occur in locations with strong electromagnetic noise, we provide fans that are unaffected by electrolytic corrosion. Alternative measures to protect against electrolytic corrosion may include metallic finger guards or other metallic attachments. Please contact us for details.

SANYO DENKI

1-15-1, Kita-otsuka, Toshima-ku, Tokyo 170-8451, Japan. PHONE : +81 3 3917 5151 Home Page: <http://www.sanyodenki.co.jp>

2006.1 Rev.A