





PRODUCT NUMBER	PITCH
YK515xx3x0J0G	9.50 mm



RECOMMENDED P.C.B LAYOUT TOP VIEW

MATERIALS & ELECTRICAL
RATED VOLTAGE & CURRENT: 300 V, 30A
WITHSTAND VOLTAGE: AC 2000 V/Min
INSULATION RESISTANCE: 1000 MΩ OR MORE AT DC 500 V
OPERATING TEMPERATURE RANG: -40 °C ~ +115 °C
SCREW TORQUE VALUE: 8.8 Lb-In.
WIRE RANGE: 10-22 AWG
1) HOUSING: Thermoplastic, UL 94 V-0 BLACK
2) TERMINAL: BRASS, 0.8t
3) TERMINAL SCREWS: STEEL, M3.5
APPROVAL: us

DIMENSION

Dim A	(N+2)×9.5+2.0
Dim B	(N-1)×9.5
Dim C	(N+1)×9.5

N=Number of poles

Poles	Tolerance
2p-3p	±0.30
4p-12p	±0.40
13p-30p	±0.60

PART NO.: YK 515xx 3 x 0 J0G

No. of poles
02 2 poles
03 3 poles
...
30 30 poles

Plated

Code	Terminal	Screw
0	G/F	G/F
1	G/F	Zinc
2	Tin	G/F
3	Tin	Zinc

RoHS compliant
(lead<4%)
In copper Alloy

mat'l. code				surface ASME Y14.5		tolerance ASME Y14.5		projection 		product family TERMINAL BLOCK										
ltr		ecn		no		dr		date		tolerances unless otherwise specified										
										angles										
										X.±0.5										
										X.X±0.3										
												X'±1°		scale		TERMINAL BLOCK				
																BARRIER TYPE,WITH FLANGE				
																dwg no				
																sheet 1 of 1				
																size				
																A4				
																type				
																CUSTOMER Drawing				
sheet index		revision sheet		A		1														