



HONEYWELL  
PART NUMBER  
311SX66-H392  
PRODUCT CODE  
VDS0424

REV	DOCUMENT	CHANGED BY	CHECK
4	0038558	SS 08MAY08	BLR



ELONGATED MTG HOLE

- NOTES
- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF  $\varnothing .087$  MAX ON  $.188 \pm .002$  CENTERS
  - 2 - TERMINALS ARE PLATED FOR SOLDERING
  - 3 - SWITCH MATERIALS WILL WITHSTAND TEMPERATURE OF 250° F

RELEASE NO.	PR-20663
REPLACES	X96084-SX

CHARACTERISTICS	
OPERATING FORCE	— — — 50 GRAM MAX
RELEASE FORCE	— — — — 9 GRAM MIN
DIFFERENTIAL TRAVEL	— — .020 MAX
OVERTRAVEL	— — — — .014 MIN

ELECTRICAL DATA			
CONTACT ARRANGEMENT SPDT			
28 VOLTS DC RATING		115 VOLTS AC, 60 CPS	
SEA LEVEL	50,000 FT	SEA LEVEL	
INDUCTIVE	3 AMP	2 AMP	5 AMP
RESISTIVE	5 AMP	4 AMP	5 AMP
APPROVALS	KEMA, CE 5A 250 V - T125 5E4 UL, CSA 5A 250 VAC    L4L		

DESIGN UNITS: INCH  
TOLERANCES UNLESS NOTED:  
NO PLACE X ±  
ONE PLACE .X ± 0.030  
TWO PLACE .XX ± 0.015  
THREE PLACE .XXX ± 0.005  
FOUR PLACE .XXXX ±  
ANGLES ±

THIRD ANGLE PROJECTION

DRAWN	SPK	26FEB08
CHECK	RJ	26FEB08
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		
RASTER		

<b>Honeywell</b>			
TITLE SWITCH - BASIC			
SIZE	TYPE	DRAWING NAME	REV
<b>B</b>	<b>I</b>	<b>311SX66-H392</b>	<b>4</b>
SCALE	-	WEIGHT:	SHEET 1 OF 1