Part Number : 2074781003
Product Description : KK Plus 396 Header, 3.96mm Pitch, Vertical, Unshrouded, Tin (Sn) Plating, 3 Circuits, with Peg
Series Number : 207478
Status : Active
Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

2074781003_sd.pdf

2074790000-PK-000.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

SYM-207478-1003-001.zip

Specifications

2074580000-AS-000.pdf

2074580000-PS-000.pdf

2074580000-PS-CH-000.pdf

2074580000-PS-JP-000.pdf

2074580000-PS-SK-000.pdf

2074580000-TS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant

Downloaded from Arrow.com.

Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)6375-DC (05 Nov 2025) SCIP:7bb16699-4335-4b7f-8304-05e7017ca0f7
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	207478
Description	KK Plus 396 Header, 3.96mm Pitch, Vertical, Unshrouded, Tin (Sn) Plating, 3 Circuits, with Peg
Application	Power, Wire-to-Board
Component Type	PCB Header
Product Name	KK Plus
UPC	191130111138

Agency

CSA	LR19980
UL	E29179

Downloaded from Arrow.com.

Electrical

Current - Maximum per Contact	11.0A
Voltage - Maximum	350V AC/DC

Physical

Breakaway	No
Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Black
Durability (mating cycles max)	25
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	Yes
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	2.457/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Tray
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
PC Tail Length	3.50mm
Pitch - Mating Interface	3.96mm
Pitch - Termination Interface	3.96mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	No
Stackable	No
Temperature Range - Operating	-40° to +105°C

Downloaded from Arrow.com.

Termination Interface Style	Through Hole

Mates With / Use With

Mates with Part(s)

Description	Part Number
KK Plus 396 Single Row Receptacle Housings	207458

This document was generated on Dec 17, 2025

Downloaded from Arrow.com.