

SOLARPOWER-HDTM Series



SOLARPOWER-HDTM Series - XUNZEL

High-Efficiency Photovoltaic Solar Panel
Ultra-Thin, Lightweight and Flexible

Product Overview

- Specially Designed to charge 12V and 24V batteries with maximum efficiency and optimum performance.
- High-Quality materials for all climatic conditions. IT WORKS!
- High-Quality Solar Cable included and pre-installed.
- Ready-to-Connect directly to the charger controller.
- Ultra-Thin (3mm), Lightweight and Flexible.
- Easy-to-install. Ready-to-connect. Stainless Steel Rings (Ø10 mm)
- Secure and easy wiring. Includes 3 meters pre-assembled 2-core, single solar cable.
- Completely Waterproof and Weatherproof junction box (IP67).
- High-Efficiency IBC all-back contact Monocrystalline Silicon Solar Photovoltaic Cells.
- Specially designed for 12V Off-Grid & Off-Shore Battery Charging Systems.
- Easy to connect in series for 24V systems.
- With high-efficiency bypass Schottky diodes included
- Higher power systems can be achieved easily connecting more strings in parallel (for more current) or series (for more voltage)
- New Design. All-Black Module
- Front-side junction box for a perfect assembly in flat surfaces
- High-performance and very reliable
- High Quality. 100% Flash and Electroluminescence-EL Tested
- With marine grade durability
- Ideal for marine, caravan, trucks, etc.


Available Models

SOLARPOWER-HD 50W-12V
SOLARPOWER-HD 120W-12V

IP67 Protection



Stainless Steel Rings Ø10mm



XU9230102MA

Industry Leading Technology for Off-Grid, Off-Shore and Backup Power Applications



© Copyright Xunzel. Information contained in this document is subject to change without notice.

SOLARPOWER-HDTM Series

Technical Specifications

Model	SOLARPOWER-HD-50W 12V	SOLARPOWER-HD-120W 12V
Part Number XUNZEL Code	SPHD05012	SPHD12012
Maximum Power P _{max}	50W	120W
Nominal Voltage	12V	
Open Circuit Voltage V _{OC}	20.80V	23.30V
Maximum Power Point Voltage V _{MPP}	17.36V	19.80V
Short-Circuit Current I _{SC}	3.11A	6.42A
Maximum Power Point Current I _{MPP}	2.88A	6.06A
Maximum System Voltage SCII	45VDC	
Cells	IBC SUNPOWER Cell III-GEN 24.40%	
Dimensions (mm)	600 x 500 x 3 mm	1100 x 560 x 3 mm
Net Weight (kg)	1.35kg	2.50kg
Pre-assembled Cables	2-core cable (3 meters) Pre-cut 1.5cm 2x1,5mm2	2-core cable (3 meters) Pre-cut 1.5cm 2x2,5mm²
Grommets	4 pcs. Stainless Steel. Inner Ø10mm	6 pcs. Stainless Steel. Inner Ø10mm
Junction Box	IP67, Front-side	
Schottky Bypass Diode	2 pc	2 pcs
Operating Temperature	-40°C to +85°C	
Temperature Coefficient of Power	-0.30%/°C	
Temperature Coefficient of V _{OC}	-1.74mV/°C	
Temperature Coefficient of I _{SC}	2.20mA/°C	
Flexible Bending	30° maximum maximum bending arch height: 40mm	
Manufactured and Tested according to IEC 61215 / IEC 61730 CE UKCA RoHS3 REACH Electrical data – Specifications at Standard Test Conditions (STC): 1000W/m₂ solar irradiance, AM 1.5, 25 °C cell temperature		



XUNZEL™ reserves the right to make changes and improvements without prior notice.

XU9230102MA

Industry Leading Technology for Off-Grid, Off-Shore and Backup Power Applications



info@xunzel.com
www.xunzel.com



© Copyright Xunzel. Information contained in this document is subject to change without notice.

Downloaded from Arrow.com



The design and all photos and drawings on these sheets are protected by law and may not be distributed or reproduced, in whole or in part, or published or used for any purpose without the express written consent of XUNZEL. XUNZEL - Xunzel is not responsible for any typographical errors. Specifications subject to change without notice.

SOLARPOWER-HDTM Series

SOLARPOWER-HD-120W 12V



SOLARPOWER-HD-50W 12V



XUNZELTM reserves the right to make changes and improvements without prior notice.

XU9230102MA

Industry Leading Technology for Off-Grid, Off-Shore and Backup Power Applications

