
THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -.-.
© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC	DIST
DF	X5

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	G	ECO 08-024363	08OCT08	MB	MZ
	G1	REVISED PER ECO-09-021510	14SEP09	KK	AEG




1. DISTANCE TO INTERFACE – REF ONLY.
2. NOMINAL WIPE EXCLUDING POST TIP – REF ONLY.
3. HOUSING MATERIAL: LCP, COLOR: BLACK.
4. CONTACT BASE MATERIAL: PSOSPHOR BRONZE.
5. CONTACT PLATING: 0.00076[.000030] MIN GOLD OVER 0.00127[.000050] MIN NICKEL IN CONTACT AREA. 0.00381[.000150] MIN HOT AIR LEVELED TIN–LEAD ON SOLDER TAILS.
6. MARKED WITH TE PART NUMBER IN APPROXIMATE AREA SHOWN.
7. RETENTION FEATURE MATERIAL: BERYLLIUM COPPER 0.250±0.013[.0100±.0005] THICK.
8. CONTACT PLATING: 0.00076[.000030] MIN GOLD OVER 0.00127[.000050] MIN NICKEL IN CONTACT AREA. 0.00381[.000150] MIN LEAD FREE MATTE TIN ON SOLDER TAILS.
9. MARKED WITH DATE CODE IN APPROXIMATE AREA SHOWN.
10. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI




VIEW L–L
SCALE 10:1



SECTION K–K
SCALE 40:1
TYP





RECOMMENDED PCB HOLE LAYOUT

10 OBSOLETE	8	72	~~646279-2~~
	5	72	646279-1
	FINISH	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES [mm]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± –
2 PLC ± 0.13 [.005]
3 PLC ± –
4 PLC ± –
ANGLES ± 2°

MATERIAL 3 4 7
FINISH SEE TABLE

DWN J ASICK	10/25/93
CHK S.HEADER	07/09/93
APVD S.HEADER	07-09-93
PRODUCT SPEC	—
APPLICATION SPEC	—
WEIGHT	—

Tyco Electronics
Tyco Electronics Corporation
Harrisburg, PA 17105-3608

NAME
Z-PACK 2mm RS
R/A PIN HEADER ASSEMBLY
SEQUENCED MATING POST LENGTH

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A1	00779	C-646279	—

CUSTOMER DRAWING | SCALE 4:1 | SHEET 1 OF 1 | REV G1

Downloaded from Arrow.com.