174259-1 DO NOT USE FOR NEW DESIGN

TE Internal #: 174259-1

TE Internal Description: E-J MK-2(+) 4P CAP HSG L-GRY ECONOSEAL, CONNECTOR HOUSING

View on TE.com >







All ECONOSEAL, CONNECTOR HOUSING (58)

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Downloaded from Arrow.com.

Compatible Parts



TE Part # CAT-EC7491-T273
Econoseal Receptacles and Tabs




TE Part # 174258-7
ECONO-J MK-2 LOCK PLATE 4P




TE Part # 171631-2
070 TAB CONT GOLD



TE Part # CAT-EC7491-CH8172
ECONOSEAL, CONNECTOR HOUSING



TE Part # 1-174260-1
ECONO-J MK-2 LOCK PLATE CAP 4P



TE Part # 174260-7
EOCNO-J MK-2 LOCK PLATE CAP 4P



TE Part # 1-900325-9
070 RUBBER PLUG M


Customers Also Bought



TE Part #184392-1
2X2 PLG ASY, KEY A, W/O CPA C3



TE Part #964269-3
TAB A 1.6x0.6 CONTACT CF SWS Au



TE Part #5-965982-1
TAB 2.8x0.8 CONTACT CF SWS Sn



TE Part #1-1437713-2
106100=GROMMET RED



TE Part #1-1456426-6
4POS, MCON 1.2 CB REC 2p TL SEALED



TE Part #2-2176092-5
RP 2A 0.25W 1K24 0.1% 25PPM 1K RL



TE Part #184400-1
2X2 PLUG ASSY, G KEY, CLASS 3,



TE Part #2203773-7
Plug Ass'y, 4P Sealed, Key G



TE Part #174259-3
EJ II+4POS CAP HSG



TE Part #184349-1
2X2 PLG ASY KEY B C3

Downloaded from Arrow.com.

Documents

Product Drawings

E-J MK-2(+) 4P CAP HSG L-GRY

Japanese

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_174259-1_F.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_174259-1_F.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_174259-1_F.3d_stp.zip

English

Customer View Model

ENG_CVM_174259-1_D.3d_igs.zip

English

Customer View Model

ENG_CVM_174259-1_D.3d_stp.zip

English

Customer View Model

ENG_CVM_174259-1_D.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

Econoseal Connector Series

English

Product Specifications

Crimping of AMP-ECONOSEAL "J"-II, .070 and .250 Series Contact

English

Application Specification

English

Instruction Sheets

ECONOSEAL J MARK II+ CONNECTOR (EJ-MK II+)

English

ECONOSEAL J MARK II+ CONNECTOR (EJ-MK II+)

English

Downloaded from Arrow.com.

ECONOSEAL J MARK II+ CONNECTOR

English

ECONOSEAL J MARK II+ CONNECTOR

English

Agency Approvals

Agency Approval Document

English

Downloaded from Arrow.com.