


[Products](#)[Industries](#)[Resources](#)[About TE](#)[Support Center](#)[My Account](#)[Home](#) > [Products](#) > [Wire & Cable](#) > [Product Feature Selector](#) > Product Details

22759/33-24-6 Product Details

[+ Share](#)[Print](#)[Email](#)

22759/33-24-6

TE Internal Number: 216442-000

 [Active](#)

Spec 44, Spec 55 and Spec RCW Wire and Cable

 [Converted to EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- Cable Type = Spec 55
- Wire Source = United States
- Cable Style = Primary
- Wire Size (AWG/CM) = 24 AWG
- Voltage Rating = 600 VAC

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)[Request Sample](#)[Find Similar Products](#)[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [WIRE, RADIATION-CROSSLINKED, MODIFIED, ETFE-INSULATE...](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Cable Type](#) = Spec 55
- [Cable Style](#) = Primary
- Number of Conductors = 1

Electrical Characteristics:

- Voltage Rating (VAC) = 600

Body Features:

- Wire Size (AWG/CM) = 24 AWG
- Conductor Type = Silver-Coated High-Strength Copper Alloy
- Wire Color = Blue
- Nominal Outside Diameter (mm [in]) = 0.94 [0.037]
- Wire Diameter (mm [in]) = 0.94 [0.037]
- Conductor O.D. (mm [in]) = 0.64 [0.025]

Industry Standards:

- Government/Industry Qualification = Yes
- Government/Industry Part Number = M22759/33-24-6
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Converted to comply with RoHS directive

Conditions for Usage:

- Temperature Range (°C) = -65 - +200
- Wire Size - Details = 24 AWG 0.24 mm², 0.00037 in², 19 x 36 AWG

Operation/Application:

- Application = General Purpose - Lightweight

Packaging Features:

- Wire Source = United States

Other:

- Brand = Raychem

Corporate Information

[Who We Are](#)[Investors](#)[News Room](#)[Supplier Portal](#)[Careers](#)

Quick Links

[Check Distributor Inventory](#)[Cross Reference](#)[Find Documents & Drawings](#)[Product Compliance Support Center](#)[Site Map](#)

Customer Support

[Email or Chat With Us](#)[Find a Phone Number](#)[Search Knowledge Base](#)[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

