


1326030 - 2 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



1326030 - 2

[Active](#)

Timer Contacts

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Contact
- ? Contact Type = USCAR
- ? Receptacle
- ? Wire Range = 0.50 - 0.90 ² [20-18] mm [AWG]
- ? Insulation Diameter = 1.20 - 4.04 mm

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [2.8mm RECEPTACLE UNSEALED](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? [2.8 mm Terminal System \(Sealed and Unsealed\)](#) (PDF, English)

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Additional Product Images:

- ? [Line Drawing](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Contact
- ? [Gender](#) = Receptacle
- ? [Insulation Diameter \(mm \[in\]\)](#) = 1.20 - 4.04 [0.047 - 0.161]
- ? [Tab Fit \(mm \[in\]\)](#) = 2.79 x 0.81 [.110 x .032]

Body Related Features:

- ? [Wire Range \(mm \[AWG\]\)](#) = 0.50 - 0.90 ² [20-18]
- ? [Single Wire Sealing System](#) = No

Contact Related Features:

- ? [Contact Type](#) = USCAR
- ? [Contact Material](#) = Copper Alloy
- ? [Contact Mating Area Plating](#) = Bright Tin

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? [RoHS/ELV Compliance History](#) = Always was RoHS compliant

Conditions for Usage:

- ? [Terminate To](#) = Wire

Packaging Related Features:

- ? [Packaging Method](#) = Tape & Reel

Other:

- ? [GET 0.64 Connector System](#) = No
- ? [Brand](#) = AMP