




Part Number : [732830311](#)
Product Description : High-Density EMI
Filtered D-Sub Adapter, Male-to-Female,
Straight, 1000pF C, 15 Circuits
Series Number : 73283
Status : Active
Product Category : D-Sub Connectors



Documents & Resources

Drawings
[732830311_sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
--------	--------

Category	D-Sub Connectors
Series	73283
Description	High-Density EMI Filtered D-Sub Adapter, Male-to-Female, Straight, 1000pF C, 15 Circuits
Component Type	Adapter
Product Name	EMI Filtered D-Sub
Type	High Density EMI Filtered
UPC	198282750918

Electrical

3 dB Cut-off Frequency Max. (MHz)	5.1
Capacitance Tolerance	± 25%
Capacitance Value	1000 pF
Current - Maximum per Contact	3.0A
Dielectric Withstanding Voltage (V)	300
EMI Filter Circuits	Capacitive
Minimum Insertion Loss (dB) - 100 MHz	20
Minimum Insertion Loss (dB) - 10 MHz	3
Minimum Insertion Loss (dB) - 1 GHz	35
Minimum Insertion Loss (dB) - 200 MHz	25
Minimum Insertion Loss (dB) - 20 MHz	8
Minimum Insertion Loss (dB) - 500 MHz	32
Minimum Insertion Loss (dB) - 50 MHz	14
Voltage - Maximum	100V DC

Physical

Circuits (Loaded)	15
Circuits (maximum)	15
Color - Resin	Blue
Durability (mating cycles max)	500
Gender	Male/Female

Material - Contact	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Polyester
Material - Shell	Zinc
Number of Rows	3
Orientation	Straight
Packaging Type	Tray
Panel Mount	Rear
Panel Mount Method	Hardware
PC Tail Length	N/A
PCB Locator	No
PCB Retention	None
Pitch - Mating Interface	2.29mm
Pitch - Termination Interface	2.29mm
Plating min - Mating	1.270µm
Plating min - Termination	Flash
Plating - Shell	Nickel
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Temperature Range - Operating	-55° to +125°C
Termination Style	N/A
Waterproof / Dustproof	No
Wire Size (AWG)	N/A

This document was generated on Mar 27, 2025