


Technical data

- 1.Nominal voltage: 300V/8A
PITCH:3.81mm
- 2.Connection capacity:
AWG 30-16
- 3.Insulation Withstanding Voltage:
AC 1600V/MIN
- 4.Insulation Resistance:
1000M Ω or more at DC500V
- 5.Tightening torque:
2.3kgf.cm (2 Lb-in / 0.23N.m)
- 6.Screw thread: M2
- 7.Stripping length: 6-7mm
- 8.Operating temperature range:-40°C ~ 115°C
- 9.Undimensioned Tolerances:

Dim.L=Px3.81 Dim.B=(P-1)x3.81 P= number of poles		
0-30mm	Dim B ± 0.15	Dim L ± 0.20
over 30mm-60mm	± 0.20	± 0.25
over 60mm-90mm	± 0.25	± 0.30
over 90mm	± 0.30	± 0.40

10.Safety approval:

11.RoHS Compliance

Part No.:

OSTTSXX315B

No. of Poles

02 2 Poles

03 3 Poles

... ..

24 24 Poles

COLOR

0: Black

2: Red

3: Orange

4: Yellow

5: Green (Standard)

6: Blue

8: Grey

Nonstandard colors
Mins could apply

5	CAGE	BRASS	M2.0x0.4, Ni PLATED	P
4	SCREW	STEEL	M2.0x0.4, Zn Plated	P
3	WIRE GUARD	BRONZE (PhBz)	TIN PLATED	P
2	COVER	PA66 UL94V-0	ALL COLOR	1
1	BODY	PA66 UL94V-0	ALL COLOR	1
ITEM	NAME OF PART	MATERIAL	NOTES	Q'TY
DWG.	WF. Zhang	DATE 2016.05.28	UNITS: MM SHEET: 1 OF 1	Tolerance
CHK.	WF. Zhang	DATE 2016.05.28	SCALE: NONE 2.5:1 (:) REV.: A	X. ± 0.50
APP.		DATE	TITLE: OSTTS 3.81 Series W/o Flange "-." Slot screw type	X.X ± 0.30
			PART NO. OSTTSXX315B	X° $\pm 1^\circ$
			DWG NO. OSTTSXX315B.dwg	
ON-SHORE TECHNOLOGY, INC.				

SIGN	DESCRIPTION	CHK.	DATE