MOSFET - Power, Single N-Channel, STD Gate, TCPAK57

80 V, 2.8 mohm, 157 A

NVMJST2D8N08X


$V_{(BR)DSS}$	$R_{DS(ON)}$ MAX	I_D MAX
80 V	2.8 mΩ @ V_{GS} = 10 V	157 A

Features


- Low Q_{RR}, Soft Recovery Body Diode
- Low $R_{DS(on)}$ to Minimize Conduction Losses
- Low Q_G and Capacitance to Minimize Driver Losses
- AECQ101 Qualified and PPAP Capable
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

Applications

- Synchronous Rectification (SR) in DC-DC and AC-DC
- Primary Switch in Isolated DC-DC Converter
- Motor Drives
- Automotive 48 V System



N−CHANNEL MOSFET



TCPAK57
CASE 760AG


MAXIMUM RATINGS (T_J = 25 °C unless otherwise noted)

Parameter		Symbol	Value	Unit
Drain-to-Source Voltage		V_{DSS}	80	V
Gate-to-Source Voltage		V_{GS}	20	V
Continuous Drain Current	T_C = 25 °C	I_D	157	A
	T_C = 100 °C		111	
Power Dissipation	T_C = 25 °C	P_D	136	W
Pulsed Drain Current	T_C = 25 °C, t_p = 100 μs	I_{DM}	483	A
Operating Junction and Storage Temperature Range		T_J, T_{stg}	−55 to +175	°C
Continuous Source-Drain Current (Body Diode)	T_C = 25 °C, V_{GS} = 0 V	I_S	157	A
Single Pulse Avalanche Energy (I_{PK} = 52 A)		E_{AS}	135	mJ
Lead Temperature for Soldering Purposes (1/8″ from case for 10 s)		T_L	260	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Surface-mounted on FR4 board using a 1 in^2, 1 oz. Cu pad
2. The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.
3. E_{AS} is based on started T_J = 25 °C, rated I_{AS}, V_{DD} = 64 V, V_{GS} = 10 V, 100% avalanche tested.

MARKING DIAGRAM



XXXX = Specific Device Code
A = Assembly Location
Y = Year
W = Work Week
ZZ = Assembly Lot Code

ORDERING INFORMATION

See detailed ordering, marking and shipping information on page 5 of this data sheet.

© Semiconductor Components Industries, LLC, 2024

Downloaded from Arrow.com.

THERMAL CHARACTERISTICS

Parameter	Symbol	Value	Unit
Thermal Resistance, Junction-to-Case	$R_{\theta JC}$	1.1	°C/W
Thermal Resistance, Junction-to-Ambient	$R_{\theta JA}$	44	

ELECTRICAL CHARACTERISTICS (T_J = 25 °C unless otherwise noted)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
OFF CHARACTERISTICS						
Drain-to-Source Breakdown Voltage	$V_{(BR)DSS}$	V_{GS} = 0 V, I_D = 1 mA, T_J = 25 °C	80			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	$\Delta V_{(BR)DSS}/\Delta T_J$	I_D = 1 mA, Referenced to 25 °C		41.8		mV/°C
Zero Gate Voltage Drain Current	I_{DSS}	V_{DS} = 80 V, T_J = 25 °C			1	μA
		V_{DS} = 80 V, T_J = 125 °C (Note 4)			250	
Gate-to-Source Leakage Current	I_{GSS}	V_{GS} = 20 V, V_{DS} = 0 V			100	nA
ON CHARACTERISTICS						
Drain-to-Source On Resistance	$R_{DS(ON)}$	V_{GS} = 10 V, I_D = 30 A, T_J = 25 °C		2.4	2.8	mΩ
Gate Threshold Voltage	$V_{GS(TH)}$	V_{GS} = V_{DS}, I_D = 184 μA, T_J = 25 °C	2.4		3.6	V
Gate Threshold Voltage Temperature Coefficient	$\Delta V_{GS(TH)}/\Delta T_J$	V_{GS} = V_{DS}, I_D = 184 μA		−8.3		mV/°C
Forward Transconductance	g_{FS}	V_{DS} = 5 V, I_D = 30 A		101		S
CHARGES, CAPACITANCES & GATE RESISTANCE						
Input Capacitance	C_{ISS}	V_{DS} = 40 V, V_{GS} = 0 V, f = 1 MHz		3192		pF
Output Capacitance	C_{OSS}			923		
Reverse Transfer Capacitance	C_{RSS}			14		
Output Charge	Q_{OSS}			66		nC
Total Gate Charge	$Q_{G(TOT)}$	V_{DD} = 40 V, I_D = 30 A, V_{GS} = 10 V		45		
Threshold Gate Charge	$Q_{G(TH)}$			9.8		
Gate-to-Source Charge	Q_{GS}			15		
Gate-to-Drain Charge	Q_{GD}			7.0		
Gate Plateau Voltage	V_{GP}			4.7		V
Gate Resistance	R_G	f = 1 MHz		0.75		Ω
SWITCHING CHARACTERISTICS						
Turn-On Delay Time	$t_{d(ON)}$	Resistive Load V_{GS} = 0/10 V, V_{DD} = 64 V, I_D = 37 A, R_G = 2.5 Ω		24		ns
Rise Time	t_r			7.4		
Turn-Off Delay Time	$t_{d(OFF)}$			37		
Fall Time	t_f			5.6		
SOURCE-TO-DRAIN DIODE CHARACTERISTICS						
Forward Diode Voltage	V_{SD}	V_{GS} = 0 V, I_S = 30 A, T_J = 25 °C		0.82	0.93	V
		V_{GS} = 0 V, I_S = 30 A, T_J = 125 °C		0.71		
Reverse Recovery Time	t_{RR}	V_{GS} = 0 V, I_S = 30 A, dI/dt = 1000 A/μs, V_{DD} = 64 V		23		ns
Charge Time	t_a			13		
Discharge Time	t_b			10		
Reverse Recovery Charge	Q_{RR}			162		nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

4. Guaranteed by design and is not production tested

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS




Figure 1. On-Region Characteristics




Figure 2. Transfer Characteristics




Figure 3. On-Resistance vs. Gate Voltage




Figure 4. On-Resistance vs. Drain Current




Figure 5. Normalized ON Resistance vs. Junction Temperature




Figure 6. Drain Leakage Current vs. Drain Voltage

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS




Figure 7. Capacitance Characteristics




Figure 8. Gate Charge Characteristics




Figure 9. Resistive Switching Time Variation vs. Gate Resistance




Figure 10. Diode Forward Characteristics




Figure 11. Safe Operating Area (SOA)




Figure 12. Avalanche Current vs. Pulse Time (UIS)

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS




Figure 13. Gate Threshold Voltage vs. Junction Temperature




Figure 14. Maximum Current vs. Case Temperature




Figure 15. Transient Thermal Response

DEVICE ORDERING INFORMATION

Device	Marking	Package	Shipping†
NVMJST2D8N08XTXG	2D88	TCPAK57 Top Cool (Pb-Free)	3000 / Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

Downloaded from Arrow.com.


REVISION HISTORY

Revision	Description of Changes	Date
0	Initial Document release.	4/24/2026
1	Maximum VSD specification updated from 1.2 V to 0.93 V.	5/1/2026


Downloaded from Arrow.com.

PACKAGE DIMENSIONS

TCPAK10 5.1x7.5, 1.0P
CASE 760AG
ISSUE D




TOP VIEW




SIDE VIEW

NOTES:
1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. UNIT DIMENSION: MILLIMETERS
3. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR BURRS. MOLD FLASH PROTRUSIONS OR GATE BURRS SHALL NOT EXCEED 0.150mm PER SIDE.
4. DIMENSIONS D AND E1 ARE DETERMINED AT THE OUTERMOST EXTREMES OF THE PLASTIC BODY.
5. OPTIONAL MOLD FEATURE.
6. LAND PAD UNDER THE PACKAGE BODY IS FOR MECHANICAL SUPPORT ONLY. SOLDER CONNECTION IS NOT REQUIRED.
7. DIMENSION A1 IS THE LEAD STAND-OFF FROM THE BOTTOM SURFACE OF THE PACKAGE BODY.




BOTTOM VIEW



LAND PAD RECOMMENDATION

*FOR ADDITIONAL INFORMATION ON OUR PB-FREE STRATEGY AND SOLDERING DETAILS, PLEASE DOWNLOAD THE ON SEMICONDUCTOR SOLDERING AND MOUNTING TECHNIQUES REFERENCE MANUAL, SOLDERRM/D.

MILLIMETERS			
DIM	MIN	NOM	MAX
A	1.30	1.35	1.45
A1	-0.05	0.00	0.05
A2	1.30	1.35	1.40
b	0.36	0.41	0.46
c	0.16	0.21	0.26
D	5.00	5.10	5.20
D1	4.02	4.12	4.22
D2	0.30	0.40	0.50
D3		0.14 REF	
E	7.40	7.50	7.60
E1	5.20	5.30	5.40
E2	3.47	3.57	3.67
E3	0.30	0.40	0.50
E4		0.17 REF	
E5		4.82 REF	
e		1.00 BSC	
e1		0.50 BSC	
k		1.03 REF	
L	0.49	0.69	0.89
L1	0.90	1.10	1.30
L2		0.25 BSC	
Q	0.60	0.65	0.70
θ	0°	2.5°	5°



DETAIL 'A'

Downloaded from Arrow.com.

onsemi, ONSEMI , and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent−Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as−is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:
Technical Library: www.onsemi.com/design/resources/technical−documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support
For additional information, please contact your local Sales Representative at www.onsemi.com/support/sales

◊

Downloaded from Arrow.com.