

- Fully encapsulated low profile plastic case
- Ultra wide 4:1 input voltage range
- Operating temperature range -40°C to $+85^{\circ}\text{C}$
- I/O isolation 2500 VDC
- Excellent efficiency up to 92 %
- Input filter to meet EN 55022, class A
- Optional DIN-Rail mount adapter
- No minimum load required
- Power good LED indicator and remote on/off function
- 3-year product warranty



The TMDC 40 Series is a range of encapsulated high performance DC/DC converter modules. With a very high efficiency of up to 92% and the use of highest reliable components these 40 W converters are available as a chassis-mount with screw terminals or PCB versions. The 8 models have a wide 4:1 input voltage range and a tight output voltage regulation. They do not need a minimum load and offer a high efficiency also at low load conditions. They feature a remote control input and a green power good LED which indicates the presence of the output voltage. Protection against overload and short circuit are standard features of these converters. EMC characteristics and safety certifications are aligned for the operation in industrial environment.

Models				
Order Code	Input Voltage Range	Output Voltage nom.	Output Current max.	Efficiency typ.
TMDC 40-2411	9 - 36 VDC (24 VDC nom.)	5.1 VDC	8'000 mA	90 %
TMDC 40-2412		12 VDC	3'330 mA	90 %
TMDC 40-2415		24 VDC	1'670 mA	90 %
TMDC 40-2418		48 VDC	835 mA	89 %
TMDC 40-4811	18 - 75 VDC (48 VDC nom.)	5.1 VDC	8'000 mA	89 %
TMDC 40-4812		12 VDC	3'330 mA	91 %
TMDC 40-4815		24 VDC	1'670 mA	92 %
TMDC 40-4818		48 VDC	835 mA	90 %

Options	
TMP-MK2	- Optional DIN-Rail Mounting Kit: www.tracopower.com/overview/tmp-mk2

Input Specifications

Input Current	- At no load	24 Vin models: 90 mA typ. 48 Vin models: 55 mA typ.
	- At full load	24 Vin models: 1'868 mA typ. 48 Vin models: 927 mA typ.
Surge Voltage		24 Vin models: 50 VDC max. (100 ms max.) 48 Vin models: 100 VDC max. (100 ms max.)
Under Voltage Lockout		24 Vin models: 7.5 VDC typ. 48 Vin models: 16 VDC typ.
Recommended Input Fuse		(The need of an external fuse has to be assessed in the final application.)
Input Filter		Internal Pi-Type

Output Specifications

Voltage Set Accuracy		±2% max.
Regulation	- Input Variation (Vmin - Vmax)	0.5% max.
	- Load Variation (0 - 100%)	1% max.
Ripple and Noise (20 MHz Bandwidth)	5.1 Vout models:	100 mVp-p max.
	12 Vout models:	150 mVp-p max.
	24 Vout models:	150 mVp-p max.
	48 Vout models:	200 mVp-p max.
Capacitive Load	5.1 Vout models:	13'600 µF max.
	12 Vout models:	2'400 µF max.
	24 Vout models:	600 µF max.
	48 Vout models:	150 µF max.
Minimum Load		Not required
Temperature Coefficient		±0.02 %/K max.
Start-up Time		30 ms max.
Short Circuit Protection		Continuous, Automatic recovery
Output Current Limitation		150% typ. of Iout max.
Overvoltage Protection		120% typ. of Vout nom. (By Zener diode)
Transient Response	- Response Deviation	5% max. (75% to 100% Load Step)
	- Response Time	250 µs typ. (75% to 100% Load Step)

Safety Specifications

Standards	- IT / Multimedia Equipment	CSA-C22.2, No. 60950-1 EN 60950-1 EN 62368-1 IEC 60950-1 IEC 62368-1 UL 60950-1 UL 62368-1
	- Certification Documents	www.tracopower.com/tmdc40-safety-cert/
Energy Source		ES1
Power Source		PS3
Pollution Degree		PD 2
Over Voltage Category		Not mains connected

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

EMC Specifications

EMI (Emissions)			EN 61000-6-4 (Generic Industrial) EN 61204-3 (Low Voltage Power Supplies) EN 55032 class A (internal filter) FCC 47 Part 15 class A (internal filter) EN 55032 class A (with external filter) FCC 47 Part 15 class A (with external filter)
	- Conducted Emissions		
	- Radiated Emissions		
		External filter proposal:	www.tracopower.com/tmdc40-emc-filter/
EMS (Immunity)			EN 55024 (IT Equipment) EN 55035 (Multimedia)
	- Electrostatic Discharge	Air:	EN 61000-4-2, ± 8 kV, perf. criteria A
		Contact:	EN 61000-4-2, ± 4 kV, perf. criteria A
	- RF Electromagnetic Field		EN 61000-4-3, 10 V/m, perf. criteria A
	- EFT (Burst) / Surge		EN 61000-4-4, ± 2 kV, perf. criteria A
			EN 61000-4-5, ± 2 kV, perf. criteria A
	- Conducted RF Disturbances		EN 61000-4-6, 10 Vrms, perf. criteria A
	- PF Magnetic Field	Continuous:	EN 61000-4-8, 30 A/m, perf. criteria A
EMC / Environmental	- Certification Documents		www.tracopower.com/tmdc40-emc-cert/

General Specifications

Relative Humidity			95% max. (non condensing)
Temperature Ranges			-40°C to +85°C
	- Operating Temperature		
	- Approved Ambient Temp.	60950-1:	+65°C max.
	- Case Temperature		+95°C max.
	- Storage Temperature		-50°C to +125°C
Power Derating			4.5 %/K above 73°C (average)
	- High Temperature	See application note:	www.tracopower.com/tmdc40-cc/
Cooling System			Natural convection (20 LFM)
Remote Control			On: 3.5 to 12 VDC or open circuit
	- Voltage Controlled Remote (passive = on)		Off: 0 to 1.2 VDC or short circuit
			Refers to 'Remote' and '-Vin' Pin
	- Off Idle Input Current		3 mA typ.
	- Remote Pin Input Current		-0.5 to 0.5 mA
Altitude During Operation			6'000 m max.
Switching Frequency			285 kHz typ. (PWM)
Insulation System			Functional Insulation
Isolation Test Voltage		- Input to Output, 60 s	2'500 VDC
Isolation Resistance		- Input to Output, 500 VDC	1'000 M Ω min.
Isolation Capacitance		- Input to Output, 100 kHz, 1 V	2'800 pF max.
Reliability		- Calculated MTBF	644'300 h (MIL-HDBK-217F, ground benign)
Environment		- Vibration	IEC 60068-2-6
Housing Material			Plastic resin (UL 94 V-0 rated)
Potting Material			Silicone (UL 94 V-0 rated)
Housing Type			Plastic Case
Mounting Type			Chassis Mount
Connection Type			Screw Terminal
Weight			162 g
Thermal Impedance		- Case to Ambient	4.75 K/W typ.

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Environmental Compliance - REACH Declaration

www.tracopower.com/info/reach-declaration.pdf

- RoHS Declaration

REACH SVHC list compliant

REACH Annex XVII compliant

www.tracopower.com/info/rohs-declaration.pdf

Exemptions: 6(c), 7(c)-I

(RoHS exemptions refer to the component concentration only, not to the overall concentration in the product (O5A rule).)

- SCIP Reference Number

79c56f45-780c-49a4-92e6-91bca3c9dcf8

Additional Information

Supporting Documents

www.tracopower.com/overview/tmdc40

Frequently Asked Questions

www.tracopower.com/glossary-faq


Glossary

www.tracopower.com/info/glossary.pdf

Service Portal

www.tracoserviceportal.com

Outline Dimensions



Dimensions in mm (inch)
Tolerances: x.x ±0.5 (±0.02)

Mounting screw locked torque: 0.49 Nm (5.0 kgfcm)

Pinout

Pin*	Function
1	Remote
2	-Vin (GND)
3	+Vin (Vcc)
4	+Vout
5	NC
6	-Vout
7	NC
8	NC

NC: Not connected

Terminal screw locked torque: 0.5 Nm max.

Wire dimension: 1.5 mm² max.

Note: The size of the wires has to be assessed in the final application.