

**Part Number :** [442626422](#)

**Product Description :** 5.33mm Pitch Crimp Terminal, Power Blade, Select Gold Strips over Tin

**Series Number :** 44262

**Status :** Active

**Product Category :** Crimp Terminals

---

## Documents and Resources

### Drawings

[442626422\\_sd.pdf](#)

[STEP AP242](#)


[SOLIDWORKS](#)

[Creo](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Crimp Terminals
Series	44262
Description	5.33mm Pitch Crimp Terminal, Power Blade, Select Gold Strips over Tin
Application	Wire-to-Wire
Product Name	N/A
UPC	800756811024

### Electrical

Current - Maximum per Contact	50.0A
Voltage - Maximum	600V AC

### Physical

Durability (mating cycles max)	500
Gender	Male
Material - Metal	Copper
Material - Plating Mating	Gold
Net Weight	1.406/g
Packaging Type	Reel
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.52-3.30mm
Wire Size (AWG)	14, 16
Wire Size mm <sup>2</sup>	N/A

---

## Application Tooling

## Global

Description	Part Number
Hand Crimp Tool for 18-14 AWG Male and Female Power Contact Terminals	<u>638195500</u>
Mini-Mac Applicator	<u>638326100</u>

---

This document was generated on Jun 02, 2026