









02 Beutel beinhaltet folgende Einzelteile:
Packaging includes following single parts:



02 Kontakte bitte separat bestellen / *Please order contacts separately:*

Size 8 (2x benötigt / 2x needed):
6mm² - VN02 036 0026 6
10mm² - VN02 036 0027 6
16mm² - VN02 036 0028 6

Size 12 (2x benötigt / 2x needed):
gestanzt / stamped (AWG 12-14): AT62-12-0166 (nickel plated) / AT62-12-0144 (gold plated)
gedreht / turned (AWG 12-14): AT62-203-12141 (nickel plated) / AT62-210-1231 (gold plated)

Size 16 (4x benötigt / 4x needed):
gestanzt / stamped (0,34-0,5mm²): AT62-16-0822 (nickel plated) / AT62-16-0844 (gold plated)
gestanzt / stamped (AWG 18-20): AT62-16-0622 (nickel plated) / AT62-16-0644 (gold plated)
gedreht / turned (AWG 16-20): AT62-201-16141 (nickel plated) / AT62-201-1631 (gold plated)

Weitere Kontakte auf Anfrage / *other contacts on request*

Polzahl *number of contacts*	2+2+4+1
Kontakte *contacts*	2x Size 8 2x Size 12 4x Size 16 1x Size 16 überbrückt / *bridged*
Bemessungsspannung (DIN EN 60664-1) *Rated voltage (DIN EN 60664-1)*	24VDC
Strombelastbarkeit bei +40°C (alle Kontakte belastet) *Current carrying capacity at 40°C* *(all contacts under load)*	2x45A (6mm²) / 2x60A (10mm²) / 2x75A (16mm²) 2x15A (2,5mm²) 4x5A (0,5mm²)
02 Max. Strombelastbarkeit der Kontakte bei +40°C *max. current carrying capacity* *of contacts at +40°C*	2x50A (6mm²) / 2x70A (10mm²) / 2x80A (16mm²) 2x25A (2,5mm²)
Verschmutzungsgrad *Pollution degree*	3
Temperaturbereich *Temperature range*	-40°C bis +125°C *-40°F up to +257°F*
Schutzgrad *protection class*	IP67 / IP6K9K (gesteckt) *IP67 / IP6K9K (mated)*
Mechanische Lebensdauer *Mechanical operations*	≥100 Steckzyklen *≥100 mating cycles*
Werkstoff Dichtungen *material gaskets*	NBR, Silikon *NBR, silicone*
Werkstoff Gehäuse *material housing*	Polyamid schwarz, UL94V-0 *polyamide black, UL94V-0*
Werkstoff Kontaktträger *material housing*	Polyamid schwarz, UL94V-0 *polyamide black, UL94V-0*
Werkstoff Wellschlauchadapter *material corrugated pipe adapter*	Polyamid schwarz, UL94V-0 *polyamide black, UL94V-0*
Werkstoff Kontakte + Oberfläche *material contacts + surface*	Kupferlegierung, vernickelt *copper alloy, nickel plated*
Verriegelung *locking*	Bajonett *Bayonet*

Stecker nach ISO 11783-2
connector acc. to ISO 11783-2

Version frei konfektionierbar mit Wellschlauchadapter
(Wellschlauch wird nicht mitgeliefert)
version free assembly with corrugated pipe adapter
(corrugated pipe not included)

Crimpausrüstung siehe Montageanleitung
- N 22 000 0028 (6mm²)
- N 22 000 0029 (10mm²)
- N 22 000 0030 (16mm²)

equipment for crimping according to assembly instruction
- *N 22 000 0028 (6mm²)*
- *N 22 000 0029 (10mm²)*
- *N 22 000 0030 (16mm²)*

Alle technischen Daten wurden unter Laborbedingungen ermittelt und können im Praxisbetrieb abweichen.
Es handelt sich bei den Angaben weder um Beschaffenheits- noch um Haltbarkeitsgarantien.
All technical data have been measured in a laboratory environment and can be different during practical usage of the product.
Any product information is for descriptive usage only and not legally binding particulary the information
does not constitute or provide any legal guarantees ("Beschaffenheitsgarantie" or "Haltbarkeitsgarantie").

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patenterteilung oder Gebrauchsmuster-Eintragung vorbehalten.

Copying of this document and giving it to others and the use or communication of the contents thereof, are forbidden without express authority. Offenders are liable to the payment of damages. All rights are reserved in the event of the grant of a patent or the registration of the utility model or design.

Index	Änderung / *Description*	Datum / *Date*	Name
03	201900126	12.07.2019	SWAHL
02	201700501	26.02.2018	RSCHÄ
01	201500766	21.04.2017	RSCHÄ

Gewicht (errechnet) / *Calc. WT*:
Prüfmaß / *Testdimension*
Teileindex / *Partindexnumber*:
Bagatelle change:

Zul. Abw. / *Tolerances*: ISO 2768-c
DIN / ISO 13715

Gez.	26.10.2016	
Drawn	RSCHAEDEL	
Status	Released	
Gepr.	18.07.2019	
Checked	MGRIMM	

Amphenol Tuchel Industrial GmbH

Maßstab / *Scale*: 1:1 | A2

CUSTOMER DRAWING

Kabeldose
female cable connector

M | AHDP06-24-91S-BS2

Blatt / *Sheet* 1 | 1 Bl.

Ers. f. / *Replacement for*:

FA12019-000718 | NXM-V02

Downloaded from Arrow.com.

AT Series™ - Contact Size 16 Options

Machined Contacts, Sockets & Pins				
Part Number	**Description**	**Size**	**AWG**	**Type**
AT60-215-1631	Male Contact - Pin, Gold-plated	16	14	Machined
AT62-209-1631	Female Contact - Socket, Gold-plated	16	14	Machined
AT60-215-16141	Male Contact - Pin, Nickel-plated	16	14	Machined
AT62-209-16141	Female Contact - Socket, Nickel-plated	16	14	Machined
AT60-202-1631	Male Contact - Pin, Gold-plated	16	16-20	Machined
AT62-201-1631	Female Contact - Socket, Gold-plated	16	16-20	Machined
AT60-202-16141	Male Contact - Pin, Nickel-plated	16	16-20	Machined
AT62-201-16141	Female Contact - Socket, Nickel-plated	16	16-20	Machined
AT60-202-1631-22	Male Contact - Pin, Gold-plated	16	22-24	Machined
AT62-201-1631-22	Female Contact - Socket, Gold-plated	16	22-24	Machined
AT60-202-16141-22	Male Contact - Pin, Nickel-plated	16	22-24	Machined
AT62-201-16141-22	Female Contact - Socket, Nickel-plated	16	22-24	Machined

Tooling - Machined Contacts		
Part	**Part Number**	**Description**
	CA-5D12	Universal Hand Crimp Tool, Size 12/16/20 (Machined contacts only)
	CA-5E12	Pneumatic Crimp Tool, Size 12/16/20 (Machined contacts only)

Contact Removal Tools		
Part	**Part Number**	**Description**
	ATRT-100	Used for removal of contacts for A Series™ products
	AT11-310-1605	Contact Removal Tool, Plastic, Size 16
	A114017	Sealing Plug, Size 16, White

Stamped & Formed Contacts, Sockets & Pins				
Part Number	**Description**	**Size**	**AWG**	**Type**
AT60-14-0144	Male Contact - Pin, Gold-plated	16	14-16	Stamped & Formed
AT62-14-0144	Female Contact - Socket, Gold-plated	16	14-16	Stamped & Formed
AT60-14-0122	Male Contact - Pin, Nickel-plated	16	14-16	Stamped & Formed
AT62-14-0122	Female Contact - Socket, Nickel-plated	16	14-16	Stamped & Formed
AT60-16-0144	Male Contact - Pin, Gold-plated	16	16-18	Stamped & Formed
AT62-16-0144	Female Contact - Socket, Gold-plated	16	16-18	Stamped & Formed
AT60-16-0122	Male Contact - Pin, Nickel-plated	16	16-18	Stamped & Formed
AT62-16-0122	Female Contact - Socket, Nickel-plated	16	16-18	Stamped & Formed
AT60-16-0644	Male Contact - Pin, Gold-plated	16	18-20	Stamped & Formed
AT62-16-0644	Female Contact - Socket, Gold-plated	16	18-20	Stamped & Formed
AT60-16-0622	Male Contact - Pin, Nickel-plated	16	18-20	Stamped & Formed
AT62-16-0622	Female Contact - Socket, Nickel-plated	16	18-20	Stamped & Formed
AT60-16-0844	Male Contact - Pin, Gold-plated	16	20-22	Stamped & Formed
AT62-16-0844	Female Contact - Socket, Gold-plated	16	20-22	Stamped & Formed
AT60-16-0822	Male Contact - Pin, Nickel-plated	16	20-22	Stamped & Formed
AT62-16-0822	Female Contact - Socket, Nickel-plated	16	20-22	Stamped & Formed

Tooling - Stamped & Formed Contacts		
Part	**Part Number**	**Description**
	MFX-3950	Crimp Die - Size 16, 18-20AWG (S&F contacts only)
	MFX-3953	Crimp Die - Size 16, 16-18AWG (S&F contacts only)
	MFX-3975	Crimp Die - Size 16, 14-16AWG (S&F contacts only)
	MFX-3990	Crimp Die - Size 16, 20-22AWG (S&F contacts only)
	ATT-16-00	Hand Crimp Tool - Size 16, 14-16AWG (S&F contacts only)
	ATT-16-01	Hand Crimp Tool - Size 16, 18-20AWG (S&F contacts only)
	ATT-1612-03	Hand Crimp Tool - Size 16, 20-22AWG (S&F contacts only)

Amphenol Sine Systems
44724 Morley Drive
Clinton Township, MI 48036 USA
www.amphenol-sine.com
09/2021

Downloaded from Arrow.com.

MagnaMate™ ATHP - DuraMate™ AHDP - DuraMate™ AHDM Series - Contact Size 12 Options

Machined Contacts, Sockets & Pins				
Part Number	**Description**	**Size**	**AWG**	**Type**
AT60-204-12141-10	Male Contact - Pin, Nickel-plated	12	10-12	Machined
AT62-203-12141-10	Female Contact - Socket, Nickel-plated	12	10-12	Machined
AT60-220-1231	Male Contact - Pin, Gold-plated	12	12-14	Machined
AT62-210-1231	Female Contact - Socket, Gold-plated	12	12-14	Machined
AT60-204-12141	Male Contact - Pin, Nickel-plated	12	12-14	Machined
AT62-203-12141	Female Contact - Socket, Nickel-plated	12	12-14	Machined

DiagnosticGrade™ Machined Contacts, Sockets & Pins • Smaller AWG for Diagnostic Applications • Gold-plated • Increased Mating Cycles • Cost-effective				
Part Number	**Description**	**Size**	**AWG**	**Type**
65-54749	Male Contact - DiagnosticGrade™, Pin, Gold-plated	12	20	Machined
AT62-210-1231-1820	Female Contact - DiagnosticGrade™, Socket, Gold-plated	12	20	Machined

Tooling - Machined Contacts		
Part	**Part Number**	**Description**
	CA-5D12	Universal Hand Crimp Tool, Size 12/16/20 (Machined contacts only)
	CA-5E12	Pneumatic Crimp Tool, Size 12/16/20 (Machined contacts only)

Contact Removal Tools		
Part	**Part Number**	**Description**
	AT11-337-1205	Contact Removal Tool, Plastic, Size 12
	A114017	Sealing Plug, Size 12, White


Stamped & Formed Contacts, Sockets & Pins				
Part Number	**Description**	**Size**	**AWG**	**Type**
AT60-12-0244	Male Contact - Pin, Gold-plated	12	10-12	Stamped & Formed
AT62-12-0244	Female Contact - Socket, Gold-plated	12	10-12	Stamped & Formed
AT60-12-0222	Male Contact - Pin, Nickel-plated	12	10-12	Stamped & Formed
AT62-12-0222	Female Contact - Socket, Nickel-plated	12	10-12	Stamped & Formed
AT60-12-0144	Male Contact - Pin, Gold-plated	12	12-14	Stamped & Formed
AT62-12-0144	Female Contact - Socket, Gold-plated	12	12-14	Stamped & Formed
AT60-12-0166	Male Contact - Pin, Nickel-plated	12	12-14	Stamped & Formed
AT62-12-0166	Female Contact - Socket, Nickel-plated	12	12-14	Stamped & Formed


Tooling - Stamped & Formed Contacts		
Part	**Part Number**	**Description**
	MFX-3973	Crimp Die - Size 12 (S&F contacts only)
	MFX-3985	Crimp Die - Size 12 (S&F contacts only) 10-12AWG -02XX Series
	ATT-12-00	Hand Crimp Tool - Size 12, 12AWG (S&F contacts only)
	ATT-12-01	Hand Crimp Tool - Size 12, 10AWG (S&F contacts only)

Amphenol Sine Systems
44724 Morley Drive
Clinton Township, MI 48036 USA
www.amphenol-sine.com
01/2022

Downloaded from Arrow.com.


Copying of this document and giving it to others and the use or communication of the contents thereof, are forbidden without express authority. Offenders are liable to the payment of damages. All rights are reserved in the event of the grant of a patent or the registration of the utility model or design.





Material: Kupferlegierung
material: copper alloy
Oberfläche: vernickelt
surface coating: nickel plated
Für Kontaktstift Ø 3,6mm
for male contact Ø 3,6mm

Anschlussquerschnitt: 6mm²
cross section: 6mm²



100 Stück in einem Beutel verpackt
100 pcs packed in one poly bag

Alle technischen Daten wurden unter Laborbedingungen ermittelt und können im Praxisbetrieb abweichen.
Es handelt sich bei den Angaben weder um Beschaffenheits- noch um Haltbarkeitsgarantien.
All technical data have been measured in a laboratory environment and can be different during practical usage of the product. Any product information is for descriptive usage only and not legally binding; particulary the information does not constitute or provide any legal guarantees ("Beschaffenheitsgarantie" or "Haltbarkeitsgarantie").

Gewicht (errechnet) / *Calc WT*:	Zul. Abw./ *Tolerances*:	Maßstab / *Scale*: 2:1	A4
Prüfmaß / *Testdimension*	ISO 2768-mH	DIN / ISO 13715	CUSTOMER DRAWING
Teileindex / *Partindexnumber*:			
Bagatelle change:			

Index	Änderung/ *Description*	Datum/ *Date*	Name
04	201900099	01.04.2019	MTOLK
03	201800125	01.03.2018	NPFEI
02	201800066	25.01.2018	NPFEI
01	201500766	31.03.2017	NPFEI

Gez. / Drawn	30.03.2017 AZN_NPFEIFFE
Status	Released
Gepr. / Checked	01.04.2019 MGRIMM

Amphenol Tuchel Industrial GmbH

Buchsenkontakt
female contact

M VN 02 036 0026 6

Blatt/ *Sheet* 1 — 1 Bl.


Ers. f. / *Replacement for*:


NXM-V04 | FAI2019-000902

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patenterteilung oder Gebrauchsmuster-Eintragung vorbehalten.

Downloaded from Arrow.com.

Copying of this document and giving it to others and the use or communication of the contents thereof, are forbidden without express authority. Offenders are liable to the payment of damages. All rights are reserved in the event of the grant of a patent or the registration of the utility model or design.






Material: Kupferlegierung
material: copper alloy
Oberfläche: vernickelt
surface coating: nickel plated
Für Kontaktstift Ø 3,6mm
for male contact Ø 3,6mm

Anschlussquerschnitt: 10mm²
cross section: 10mm²

100 Stück in einem Beutel verpackt
100 pcs packed in one poly bag



Alle technischen Daten wurden unter Laborbedingungen ermittelt und können im Praxisbetrieb abweichen. Es handelt sich bei den Angaben weder um Beschaffenheits- noch um Haltbarkeitsgarantien.
All technical data have been measured in a laboratory environment and can be different during practical usage of the product. Any product information is for descriptive usage only and not legally binding; particulary the information does not constitute or provide any legal guarantees ("Beschaffenheitsgarantie" or "Haltbarkeitsgarantie").

Gewicht (errechnet) / *Calc WT* :	Zul. Abw./ *Tolerances* :	Maßstab / *Scale* : 2:1	A4
Prüfmaß / *Testdimension*	ISO 2768-mH	DIN / ISO 13715	CUSTOMER DRAWING
Teileindex / *Partindexnumber:*			
Bagatelle change:			

Index	Änderung/ *Description*	Datum/ *Date*	Name
04	201900099	01.04.2019	MTOLK
03	201800125	01.03.2018	NPFEI
02	201800066	25.01.2018	NPFEI
01	201500766	31.03.2017	NPFEI

Gez. / Drawn	30.03.2017 AZN_NPFEIFFE
Status	Released
Gepr. / Checked	01.04.2019 MGRIMM

Amphenol Tuchel Industrial GmbH

Buchsenkontakt
female contact

M VN 02 036 0027 6

Blatt/ *Sheet* 1 / 1 Bl.

Ers. f. / *Replacement for* :

NXM-V03 FA12019-000905


Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patenterteilung oder Gebrauchsmuster-Eintragung vorbehalten.


Downloaded from Arrow.com.

Copying of this document and giving it to others and the use or communication of the contents thereof, are forbidden without express authority. Offenders are liable to the payment of damages. All rights are reserved in the event of the grant of a patent or the registration of the utility model or design.

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patenterteilung oder Gebrauchsmuster-Eintragung vorbehalten.

INDUSTRIAL@AMPHENOL
TRUSTED GLOBALLY






Material: Kupferlegierung
material: copper alloy
Oberfläche: vernickelt
surface coating: nickel plated
Für Kontaktstift Ø 3,6mm
for male contact Ø 3,6mm

Anschlussquerschnitt: 16mm²
cross section: 16mm²

100 Stück in einem Beutel verpackt
100 pcs packed in one poly bag



Alle technischen Daten wurden unter Laborbedingungen ermittelt und können im Praxisbetrieb abweichen.
Es handelt sich bei den Angaben weder um Beschaffenheits- noch um Haltbarkeitsgarantien.
All technical data have been measured in a laboratory environment and can be different during practical usage of the product. Any product information is for descriptive usage only and not legally binding, particulary the information does not constitute or provide any legal guarantees ("Beschaffenheitsgarantie" or "Haltbarkeitsgarantie").

Gewicht (errechnet) / *Calc WT*:		Zul. Abw./ *Tolerances*:	DIN / ISO 13715
Prüfmaß / *Testdimension*		ISO 2768-mH	
Teileindex / *Partindexnumber*:			
Bagatelle change:			

Maßstab / *Scale*: 2:1 | A4

CUSTOMER DRAWING

Gez.	30.03.2017
Drawn	AZN_NPFEIFFE
Status	Released
Gepr.	01.04.2019
Checked	MGRIMM

Buchsenkontakt
female contact

Index	Änderung/ *Description*	Datum/ *Date*	Name
04	201900099	01.04.2019	MTOLK
03	201800125	01.03.2018	NPFEI
02	201800066	25.01.2018	NPFEI
01	201500766	31.03.2017	NPFEI

Amphenol Tuchel Industrial GmbH

M VN 02 036 0028 6

Blatt/ *Sheet* 1 | 1 Bl.

Ers. f. / *Replacement for*:

NXM-V03 | FA12019-000907

Downloaded from Arrow.com.