



Pushing Performance
Since 1945

Han-Eco 10B-HSM2-with SL-M20



Image is for illustration purposes only. Please refer to product description.

Part number	19 43 010 0290
Specification	Han-Eco 10B-HSM2-with SL-M20
HARTING eCatalogue	https://b2b.harting.com/19430100290

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Eco® B
Type of hood/housing	Surface mounted housing

Version

Size	10 B
Version	Side entry
Cable entry	2x M20
Locking type	Single locking lever

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP66

Material properties

Material (hood/housing)	Polyamide (PA) Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
Colour (seal)	RAL 9005 (jet black)
Material (locking)	Polyamide (PA) Fibre-glass reinforced



Pushing Performance
Since 1945

Material properties

Colour (locking)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0
Material flammability class acc. to UL 94 (locking levers)	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	5dbb3851-b94e-4e88-97a1-571845975242
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 61984
	EN 45545-2 Fire protection on railway vehicles
Approvals	CE

Commercial data

Packaging size	1
Net weight	238.2 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140178298
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors