




NOTES:

1. MATERIALS AND FINISHES:
BODY - BRASS, NICKEL PLATING.
CONTACT - BRASS, GOLD PLATING.
INSULATOR - PTFE
2. ELECTRICAL:
A. IMPEDANCE: 50 OHM
3. MECHANICAL:
A. DURABILITY: 500 CYCLES MIN.
B. TEMPERATURE RANGE: -65° C TO +165° C
4. PACKAGING:
A. QUANTITY: SINGLE PACK
B. MARKING: BAG TO BE MARKED
"AMPHENOL RF, 903-375J-53P, AND DATE CODE"



**RECOMMENDED
MOUNTING HOLE DIMENSIONS**



CUSTOMER OUTLINE DRAWING
ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES AND TOLERANCES ARE:
2 PLACE DECIMAL 3 PLACE DECIMAL ANGLES
±.015 (0.381 mm) ±.005 (0.127 mm) ± 1°

NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

MATERIAL
SEE NOTES

REFERENCE

EAR 111-961561-1
615X-1052-100

DRAWN
BALAJI M
DATE
09-Jul-09

ENGINEER
P. BRENZEL
DATE
4/20/90

APPROVED
K. CAPOZZI
DATE
5/19/11

CAD FILE

TITLE
SMB JACK
BULKHEAD MOUNT
PCB RECEPTACLE

Amphenol RF
Danbury, CT, USA
Tainan, Taiwan
Shenzhen, China
WWW.amphenolrf.com

SCALE: 10.0:1 SHEET 2 OF 2

REV G
DRAWING NO. 903-375J-53P
CODE ID 74868 DWG SIZE B