




PRODUCT NUMBER	PITCH
YK333xx0x0J0G	8.25 mm



MATERIALS & ELECTRICAL
 RATED VOLTAGE & CURRENT:
 WITHSTAND VOLTAGE:
 INSULATION RESISTANCE:
 OPERATING TEMPERATURE RANG:
 SCREW TORQUE VALUE:
 WIRE RANGE:
 1) HOUSING:
 2) TERMINAL:
 3) TERMINAL SCREWS:
 APPROVAL:  

cULus / CQC
 300 V, 20 A / 300 V, 32 A
 AC 2500V/Min
 1000 MΩ OR MORE AT DC 500 V
 -40 °C +115 °C
 8.8 Lb-In
 22 - 12 AWG
 Thermoplastic, UL 94 V-0 BLACK
 BRASS, 0.8t
 STEEL, M3

DIMENSION

Dim A	N×8.25±2.0
Dim B	(N-1)×8.25

N=Number of poles

Poles	Tolerance
2p-5p	±0.20
6p-10p	±0.25
11p-16p	±0.35
17p-24p	±0.40
25p-32p	±0.50

PART NO.: YK 333xx 0 x 0 J0G

No. of poles
 02 2 poles
 03 3 poles
 ...
 32 32 poles

Plated

Code	Terminal	Screw
0	G/F	G/F
1	G/F	Zinc
2	Tin	G/F
3	Tin	Zinc

RoHS compliant
 (lead<4%)
 In copper Alloy

mat'l. code				surface ASME Y14.5 ✓		tolerance ASME Y14.5		projection 		product family TERMINAL BLOCK																	
ltr		ecn no		dr		date		tolerances unless otherwise specified				title		TERMINAL BLOCK BARRIER TYPE													
								angles		linear		MM															
										X.±0.5																	
										X.X±0.3																	
										X'±1"		X.XX±0.1		scale													
										dr		EVAN LU		061614				dwg no		sheet 1 of 1				size			
										engr		EVAN LU		061614				YK333xx0x0J0G		A4							
										chr		HANKE FENG		061614													
										appd		SHI JUN		061614													
sheet index		revision sheet		A 1																							