

Part Number : 1202310059
Product Description : Brad M23 Signal Connector, Front Panel-Mount Receptacle, 90° Male Flange Mount 4xØ 2.70mm, Rotatable, Crimp Contacts, 17 Poles
Series Number : 120231
Status : Obsolete
Product Category : Industrial Connectors
Engineering Part Number : KRSJG27-0112

Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Obsolete

Downloaded from Arrow.com.

Part Details

General

Status	Obsolete
Category	Industrial Connectors
Series	120231
Description	Brad M23 Signal Connector, Front Panel-Mount Receptacle, 90° Male Flange Mount 4xØ 2.70mm, Rotatable, Crimp Contacts, 17 Poles
Comments	Crimp Range 0.14-1.00mm^2
IP Rating	IP67
Product Name	Brad M23
Type	Field Attachable Connector
UPC	883906300340

Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	150V

Physical

Cable Diameter	N/A
Coupling Type	N/A
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Male
Keyway	None
Material - Connector Body	Nylon
Material - Contact	Brass
Material - Coupling Nut	N/A
Material - Plating Mating	Gold
Net Weight	1.000/g
Orientation	90° Angle
Poles	17
Temperature Range - Operating	-40° to +125°C

Obsolete

Downloaded from Arrow.com.

Wire Size (AWG)	N/A

This document was generated on Oct 19, 2026

Obsolete

Downloaded from Arrow.com.