

CG [Low ESR & High Ripple Current]

105°C, 2000 Hours and Ultra Low ESR

Conductive Polymer Solid Capacitors

ELECTRICAL CHARACTERISTICS

Operation Temperature Range	-55 ~ +105°C		
Rated Voltage Range	2.5 ~ 25VDC		
Rated Capacitance Range	33 ~ 2700μF		
Capacitance Tolerance	± 20% at 120Hz, 20°C		
Leakage Current (Max. 20°C)	$I \leq 0.2CV$ (μA) (After Rated Voltage Applied for 2 Minutes) I = Leakage Current (μA), C = Rated Capacitance (μF), V = Rated Voltage (V)		
Dissipation Factor at 120Hz, 20°C	WV(V)	2.5 ~ 10V	16 ~ 25
	D.F (%)	8	12
Low Temperature Stability	Impedance Ratio at 20°C (Max.)		
	WV (V)	2.5 ~ 16V	
	Impedance	Z - 25°C / Z + 20°C	≤ 1.15
		Z - 55°C / Z + 20°C	≤ 1.25 (Z: 100KHz)
Endurance	After the rated voltage has been applied at 105°C for 2000 hours, the capacitors shall meet the follow requirements. (a) Appearance: No Significant Damage (b) Capacitance Change: Within ±20% of Initial Value (c) Dissipation Factor: Not Exceeding 150% of the Initial Specified Value (d) Equivalent Series Resistance: Not Exceeding 150% of the Initial Specified Value (e) Leakage Current: Not Exceeding the Initial Specified Value		
Humidity Test	After subjected to 90 to 95% RH for 1000 hours at 60°C, the capacitors shall meet the requirements as Endurance.		



DESCRIPTION

Long life for 2000 hours at 105°C, ideally suited for high quality and high reliability applications.


Featuring high CV products

DIAGRAM OF DIMENSIONS


Unit: mm

Rubber Stand-off

Dø	P	a (Max.)
6	2.5	1.0
8	3.5	
10	5.0	



MARKING





CASE SIZE & PERMISSIBLE RIPPLE CURRENT OF STANDARD PRODUCTS

D x L: mm

CAP. (μF)	RATED VOLTAGE WV (SURGE VOLTAGE WV)								
	2.5 SIZE	RIPPLE	ESR	4 SIZE	RIPPLE	ESR	6.3 SIZE	RIPPLE	ESR
180									
270							6.3 x 10.5	3160	28.00
330							6.3 x 10.5	3190	28.00
390				6.3 x 10.5	3160	20.00	6.3 x 10.5	3190	28.00
470							8 x 11.5	5600	7.00
560	6.3 x 10.5	3160	20.00	6.3 x 10.5	3160	20.00			
680				8 x 11.5	5600	7.00			
820	6.3 x 10.5	3160	20.00				8 x 11.5	5600	7.00
							10 x 11.5	5050	7.00
1000	8 x 11.5	5600	7.00				10 x 11.5	5050	7.00
							10 x 12.5	5600	7.00
1200				8 x 11.5	5600	7.00	10 x 12.5	5600	7.00
				10 x 11.5	5050	7.00			
1500	8 x 11.5	5600	7.00	10 x 11.5	5050	7.00			
	10 x 11.5	5050	7.00	10 x 12.5	5600	7.00			
1800	10 x 12.5	5600	7.00	10 x 12.5	5600	7.00			
2700	10 x 12.5	5600	7.00						

Note: 1. Ripple Current: (mA/rms) 105°C, 100KHz

2. ESR: 100KHz / 20°C (mΩ)

CASE SIZE & PERMISSIBLE RIPPLE CURRENT OF STANDARD PRODUCTS

D x L: mm

CAP. (μF)	RATED VOLTAGE W V (SURGE VOLTAGE W V)								
	10 SIZE	RIPPLE	ESR	16 SIZE	RIPPLE	ESR	25 SIZE	RIPPLE	ESR
33							8 x 11.5	2980	30.00
47							8 x 11.5	2980	30.00
56							8 x 11.5	2980	30.00
100				6.3 x 10.5	2820	25.00			
150				6.3 x 10.5	2820	25.00			
180	6.3 x 10.5	2820	25.00	8 x 11.5	4360	16.00			
220	6.3 x 10.5	2820	25.00	8 x 11.5	5000	11.00			
270				8 x 11.5	5000	11.00			
330	8 x 11.5	5600	7.00	8 x 11.5	5000	8.00			
				10 x 11.5	4000	10.00			
				10 x 12.5	6100	10.00			
390				10 x 12.5	5050	14.00			
470	8 x 11.5	5600	7.00	10 x 12.5	5050	14.00			
	10 x 11.5	4000	7.00						
560	10 x 12.5	5050	7.00	10 x 12.5	5050	14.00			
820	10 x 12.5	5050	7.00						

Note: 1. Ripple Current: (mA/rms) 105°C, 100KHz

2. ESR: 100KHz / 20°C (mΩ)