OMRON Industrial Automation



E32-L25L 2M

Fiber optic sensor head, limited reflective, square, top-view, R10 fiber, 2 m cable

Downloaded from Arrow.com.

Specifications

Sensing method	Limited reflective
Shape	Square
Product Width (unpacked)	18 mm
Product Depth (unpacked)	4 mm
Product Height (unpacked)	16 mm
Application	Object detection
Temperature range	-40-70 °C
Sensing distance	7 mm
Cable length	2 m
Sleeve diameter	-8888 mm
Sleeve length	-8888 mm
Bending radius	10 mm
Free cut	✔
Material core	Plastic
Degree of protection (IP)	IP50
Sensing surface orientation	Top-view
Material sheath	Polyethylene

Downloaded from Arrow.com.

Related products



E3X-ZV and E3X-MZV
Smart Fiber Amplifier



E3NX-CA
High-performance color mark sensor



E3NX-CA
High-performance color mark sensor



E3NX-MA
Smart Fiber Amplifier Units



E3X-NA
Digital fiber amplifier with potentiometer adjustment



E3NX-FA
High-performance digital fiber amplifier

Downloads

CAD file



Fiber Sensor Selection
Selection Guide

EN PDF 15.9 MB

Downloaded from Arrow.com.

TERMS OF WEBSITE USE

This PDF document was created from the European OMRON Industrial Automation website on 22 October, 2026. Click here for terms of use.

OMRON

INDUSTRIAL AUTOMATION | INDUSTRIAL.OMRON.EU

Downloaded from Arrow.com.