

Part Number : 2067640050

Series Number : 206764

Product Category : Antennas

Product Description : ISM 868/915MHz Dipole Flexible Antenna, 50.00mm Cable Length, Compatible with U.FL / I-PEX MHF Connectors

Status : Active

Documents & Resources

Drawings

Drawing 2067640050_sd.pdf

Packaging Design Drawing 2067640100-PK.pdf

3D Models and Design Files

3D Model 2067640050_stp.zip

Specifications

Application Specification 2067640100-AS.pdf

Product Specification 2067640100-PS.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Antennas
Series	206764
Description	ISM 868/915MHz Dipole Flexible Antenna, 50.00mm Cable Length, Compatible with U.FL / I-PEX MHF Connectors
Component Type	Flexible Antenna with Cable
Function	Signal
Product Family	Industrial, Scientific and Medical (ISM) Antennas
Product Name	ISM 868/915 MHz Stand Alone
Protocol	LoRa, Neul, SigFox, Z-Wave, Zigbee
Type	Internal, ISM Antenna, LPWAN
UPC	191128789158

Electrical

Band#1 F_End (MHz)	870
Band#1 F_Start (MHz)	863
Band#2 F_End (MHz)	928
Band#2 F_Start (MHz)	902
Electrical Connectivity	Cable
Peak Gain (dBi)	1.3 @ 868/915 MHz
Return Loss - S11 (dB)	< -9
Total Efficiency	>71% @ 868/915 MHz

Physical

Cable Length	50.00mm
Length	87.40mm
Mounting Style	Adhesive

Net Weight	0.745/g
Packaging Type	PET Film
Polarization	Linear
Radiation Pattern	Omnidirectional
Thickness	0.10mm
Width	12.40mm

Mates With / Use With

Mates with Part(s)

Description	Part Number
50 Ohms, MCRF, PCB Vertical Jack Receptacle, SMT, 1.25mm Mounted Height	<u>734120110</u>

This document was generated on Jul 29, 2024