

60320-2 ✓ ACTIVE

AMPLIVAR


TE Internal #: 60320-2

Closed Ring Tongue Terminal, 18 – 14 AWG, #8 / M4 Stud, 4.17 mm [.164 in] Stud Diameter, Open Barrel, Straight, Tin Plating, Uninsulated, AMPLIVAR

[View on TE.com >](#)



Terminals & Splices > Ring Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 1624 – 4109 CMA

Stud Size: #8, M4

Features

Product Type Features

Shape Description	RING-028
Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	#8, M4
Sealable	No
Compatible With Discrete Wire Type	Magnet Wire
Wire Insulation Support Retention Type	Insulation Support

Configuration Features

Number of Holes	1
-----------------	---

Contact Features

Barrel Type	Open
Terminal Orientation	Straight
Terminal Plating Material	Tin
Contact Underplating Material	Brass

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------



Dimensions

Wire Size	1624 – 4109 CMA
Stud Diameter	4.17 mm [.164 in]
Tongue Thickness	.5 mm [.02 in]
Product Length	21.15 mm [.831 in]
Barrel Inside Diameter	1.27 mm, 2.92 mm [.05 in] [.115 in]
Compatible Insulation Diameter (Max)	3.56 mm [.14 in]
Compatible Insulation Diameter Range	2.54 – 3.56 mm [.1 – .14 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 105 °C [-40 – 221 °F]

Operation/Application

Compatible With Wire Base Material	Aluminum, Copper
------------------------------------	------------------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	10000
Packaging Method	Reel

Product Compliance
















[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


 <p>TE Part # 1930001-1 Amplivar, (M3.5) Ring Tongue</p>	 <p>TE Part # 2150404-2 OCEAN_2.0_Applicator-E-110F155F-REA</p>	 <p>KIT REPRESENTATION ONLY</p> <p>TE Part # 7-2150404-7 OCEAN_2.0_SPARE_PART_KIT-110F155F</p>	 <p>TE Part # 63399-1 AMPLIVAR RING 22-29 10 TPBR</p>
 <p>TE Part # 63612-1 RING AMVAR 22-18 025TPBR</p>	 <p>TE Part # 485079-1 RING AMVAR 18-14 IS 8 028 LUBZ</p>	 <p>TE Part # 60321-2 AMPLIVAR RG 23-19 8 TPBR</p>	 <p>TE Part # 63649-1 RING AMVAR 22-18 025TPBR</p>
 <p>TE Part # 62755-1 RING AMVAR 14-12 2 15025 BR</p>	 <p>TE Part # 63446-2 AMVAR RING 22-18 025TPBR</p>	 <p>TE Part # 505044-1 STUD RTNG AMVAR TERM .020 BR</p>	 <p>TE Part # 485044-1 RING AMVAR 18-14 IS 8 028LUBZ</p>
 <p>TE Part # 63446-1 AMVAR RING 22-18 025BR</p>	 <p>TE Part # 62835-1 RING AMVAR 22-18 025 TPBR</p>	 <p>TE Part # 63147-1 AMVAR RING 13 1/2-17 020BR</p>	



Also in the Series | AMPLIVAR




Crimp Wire Pins, Tabs & Ferrules(4)



Magnet Wire Terminals(4)



PCB Terminals(1)



Quick Disconnects(35)



Ring Terminals(26)



Splices(68)

Customers Also Bought



TE Part #8918194004
HCTE-0750-0-SP



TE Part #5052994173
RNF-100-1/8-BK-SP



TE Part #1060-14-0144
PIN, SF, SIZE 16, 14-18, AU/SN



TE Part #6638954004
HCTE-0500-0-SP



TE Part #DTHD06-1-4S-E003
PLG, 1P, BLK, N, SIZE 4, CAP




TE Part #6790994004
HCTE-0187-0-SP




TE Part #8-52949-1
PG SPR SPD 22-16COMM22-18MIL 6



TE Part #170889-2
SLEEVE DIA 5 SHUR PLUG NAT



TE Part #801658-SF
IB3-10



TE Part #172775-1
MIC MK-2 REC B TYPE



Documents

Product Drawings

[AMPLIVAR RG 18-14 #8 TPBR](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_60320-2_Y.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_60320-2_Y.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_60320-2_Y.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English