



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION


© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED

CONNECTOR ASSEMBLY
EXEMPLARY LOADED 



CONTACT DIMENSIONS

SCALE 5:1




CONTACT LAYOUT

	z	a	b	c	d	e	f
1		C	B	A	B	C	
2		C	B	A	B	C	
3		C	B	A	B	C	
4		C	B	A	B	C	
5		C	B	A	B	C	
6		C	B	A	B	C	
7		C	B	A	B	C	
8		C	B	A	B	C	
9		C	B	A	B	C	
10		C	B	A	B	C	
11		C	B	A	B	C	
12		C	B	A	B	C	
13		C	B	A	B	C	
14		C	B	A	B	C	
15		C	B	A	B	C	
16		C	B	A	B	C	
17		C	B	A	B	C	
18		C	B	A	B	C	
19		C	B	A	B	C	
20		C	B	A	B	C	
21		C	B	A	B	C	
22		C	B	A	B	C	
23		C	B	A	B	C	
24		C	B	A	B	C	
25		C	B	A	B	C	


RECOMMENDED PCB-HOLE LAYOUT
COMPONENT SIDE SHOWN

PLATED THRU HOLES PARAMETERS

REFERENCE APPLICATION SPECIFICATION



  	1-5352194-9
  	5352194-9
 	5352194-4
 	5352194-1
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN 30AUG05 B CARBO OK 30AUG05 C SKIPPER APVD 30AUG05 G SKIPPER PRODUCT SPEC 108-19082 APPLICATION SPEC 114-19029		 Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0-PLC ±.2 1-PLC ±.01 2-PLC ±.01 3-PLC ±.01 4-PLC ±.01 ANGLES ±.01 FINISH SEE TABLE		NAME MALE ASSEMBLY, Z-PACK 2mm HM, TYPE B	
MATERIAL 		WEIGHT —		SIZE A1	
				CAD CODE 00779	
				DRAWING NO C-5352194	
				RESTRICTED TO —	
CUSTOMER DRAWING				SCALE 4:1 SHEET 1 OF 2 REV A	

87654321

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOCAD

DIST00

REVISIONS					
REV	LTR	DESCRIPTION	DATE	DWN	APVD
—	—	SEE SHEET 1	—	—	—

1

MATERIAL:
CONTACT: PHOSPHOR BRONZE.
HOUSING: GLASS-FILLED POLYESTER.

2

GENERAL PLATING SPECIFICATION: UNDERPLATING
(ENTIRE CONTACT): 1.27μm MIN NICKEL AND ACTION
PIN: 0.5μm MIN TIN.
FOR PLATING OF MATING SURFACES SEE APPLICABLE
SPECIFICATION REFERENCE FOR EACH DASH NUMBER.

3

CONFORMS TO ALL TESTING ACCORDING TO IEC 61076-4-101
PERFORMANCE LEVEL 2.

4

CONFORMS TO ALL TESTING ACCORDING TO IEC 61076-4-101
PERFORMANCE LEVEL 1.

5

CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL 3,
CENTRAL OFFICE APPLICATIONS.

6

CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL 3,
UNCONTROLLED ENVIROMENT APPLICATIONS.

7

CONNECTOR MARKED WITH PART NUMBER AND DATE CODE.
ADDITIONAL CHARACTERS OR MARKINGS, AS WELL AS THE LOCATION OF THE MARKINGS,
MAY BE ADDED FOR TRACEABILITY BASED UPON MANUFACTURERS DISCRETION.

8

PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID
PATTERN DEFINED BY CONTACT LAYOUT.

9

FOR ACTUAL PIN LOADING SEE "CONTACT LAYOUT".

10

FOR ACTUAL PIN DIMENSIONS SEE "CONTACT DIMENSIONS".

11

TO BE MEASURED AT BOTTOM OF SHROUD.

12

CONNECTOR LUBRICATED WITH BELCORE APPROVED LUBRICANT,
TECHNICAL REFERENCE: TR-NWT-001217 ISSUE 1, SEP 1992.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

0-PLC

1-PLC

2-PLC

3-PLC

4-PLC

ANGLES

±

± 0.1

±

±

±

±

±0.2

DWN
B CARBO
CHK
G SKIPPER
APVD
G SKIPPER
PRODUCT SPEC

108-19082
APPLICATION SPEC
114-19029

WEIGHT
—

MALE ASSEMBLY, Z-PACK 2mm HM,
TYPE B

SIZE
A1

CAGE CODE
00779

DRAWING NO
5352194

RESTRICTED TO
—

CUSTOMER DRAWING

SCALE
4:1

SHEET
2

OF
2

REV
A