
Part Number : 11020022
Product Description : Insertion Tool for 70021,70028, 70110, 71851 Terminals / Extraction Tool for 91821 Terminals
Series Number : 207121
Status : Active
Product Category : Crimp Presses and Crimp Hand Tools
Engineering Part Number : HTA60615



Documents and Resources

Tooling Specifications

ATS-011020022-001.pdf
TM-638000029-001.pdf
TM-638000029DE-001.pdf
TM-638000029SP-001.pdf
TM-638000029FR-001.pdf
TM-638000029IT-001.pdf
TM-638000029JP-001.pdf
TM-638000029KR-001.pdf
TM-638000029MY-001.pdf
TM-638000029PL-001.pdf
TM-638000029RU-001.pdf
TM-638000029SK-001.pdf
TM-638000029TH-001.pdf
TM-638000029VN-001.pdf
TM-638000029CN-001.pdf
TM-638000029TW-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant

Downloaded from Arrow.com.

Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Presses and Crimp Hand Tools
Series	207121
Description	Insertion Tool for 70021,70028, 70110, 71851 Terminals / Extraction Tool for 91821 Terminals
Function	Insertion
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	N/A
Tool Type	Insertion Hand Tool
UPC	800753609471
Warranty Disclaimer	CAUTION: Molex tooling crimp

Downloaded from Arrow.com.

	specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight	2.920/zg

Applicable Parts

Description	Part Number
SL Crimp Terminal, Series 70058, Female, 30-24 AWG, with Tin (Sn) Plated Contact, Reel	16020069
SL Crimp Terminal, Series 70058, Female, 36-32 AWG, with 0.38µm Selective Gold (Au) Plated Contact, Reel	16020074
SL Crimp Terminal, Series 70021, Male, 8.43mm Mating Length, 0.38µm Gold (Au) Plated, 30-24 AWG, Reel	16020077
SL Crimp Terminal, Series 70021, Male, 8.43mm Mating Length, 0.76µm Gold (Au) Plated, 30-24 AWG, Reel	16020078
SL Crimp Terminal, Series 70021, Male, 8.43mm Mating Length,	16020079

Downloaded from Arrow.com.

0.38µm Gold (Au) Plated, 36-32 AWG, Reel	
SL Crimp Terminal, Series 70021, Male, 8.43mm Mating Length, 0.76µm Gold (Au) Plated, 36-32 AWG, Reel	16020080
SL Crimp Terminal, Series 70021, Male, 8.43mm Mating Length, 0.38µm Gold (Au) Plated, 24-22 AWG, Reel	16020081
SL Crimp Terminal, Series 70058, Female, 30-24 AWG, with 0.38µm Selective Gold (Au) Plated Contact, Reel	16020082
SL Crimp Terminal, Series 70058, Female, 30-24 AWG, with 0.76µm Selective Gold (Au) Plated Contact, Reel	16020083
SL Crimp Terminal, Series 70058, Female, 36-32 AWG, with 0.76µm Selective Gold (Au) Plated Contact, Reel	16020085
SL Crimp Terminal, Series 70058, Female, 24-22 AWG, with Tin (Sn) Plated Contact, Reel	16020086
SL Crimp Terminal, Series 70058, Female, 24-22 AWG, with 0.38µm Selective Gold (Au) Plated Contact, Reel	16020087
SL Crimp Terminal, Series 70058, Female, 24-22 AWG, with 0.76µm Selective Gold (Au) Plated Contact, Reel	16020088
SL Crimp Terminal, Series 70058, Female, 30-24 AWG, with Tin (Sn) Plated Contact, Bag	16020096
SL Crimp Terminal, Series 70058, Female, 30-24 AWG, with 0.38µm Selective Gold (Au) Plated Contact, Bag	16020097
SL Crimp Terminal, Series 70058, Female, 30-24 AWG, with 0.76µm	16020098

Downloaded from Arrow.com.

Selective Gold (Au) Plated Contact, Bag	
SL Crimp Terminal, Series 70058, Female, 36-32 AWG, with 0.76µm Selective Gold (Au) Plated Contact, Bag	16020101
SL Crimp Terminal, Series 70058, Female, 24-22 AWG, with Tin (Sn) Plated Contact, Bag	16020102
SL Crimp Terminal, Series 70058, Female, 24-22 AWG, with 0.38µm Selective Gold (Au) Plated Contact, Bag	16020103
SL Crimp Terminal, Series 70058, Female, 24-22 AWG, with 0.76µm Selective Gold (Au) Plated Contact, Bag	16020104
SL Crimp Terminal, Series 70021, Male, 8.43mm Mating Length, Tin (Sn) Plated, 30-24 AWG, Reel	16020105
SL Crimp Terminal, Series 70021, Male, 8.43mm Mating Length, Tin (Sn) Plated, 36-32 AWG, Reel	16020106
SL Crimp Terminal, Series 70021, Male, 8.43mm Mating Length, Tin (Sn) Plated, 24-22 AWG, Reel	16020107
SL Crimp Terminal, Series 70021, Male, 8.43mm Mating Length, Tin (Sn) Plated, 30-24 AWG, Bag	16020108
SL Crimp Terminal, Series 70021, Male, 8.43mm Mating Length, 0.38µm Gold (Au) Plated, 30-24 AWG, Bag	16020109
SL Crimp Terminal, Series 70021, Male, 8.43mm Mating Length, 0.76µm Gold (Au) Plated, 30-24 AWG, Bag	16020110
SL Crimp Terminal, Series 70021, Male, 8.43mm Mating Length, Tin (Sn) Plated, 36-32 AWG, Bag	16020111
SL Crimp Terminal, Series 70021, Male, 8.43mm Mating Length,	16020112

Downloaded from Arrow.com.

0.38µm Gold (Au) Plated, 36-32 AWG, Bag	
SL Crimp Terminal, Series 70021, Male, 8.43mm Mating Length, 0.76µm Gold (Au) Plated, 36-32 AWG, Bag	16020113
SL Crimp Terminal, Series 70021, Male, 8.43mm Mating Length, Tin (Sn) Plated, 24-22 AWG, Bag	16020114
SL Crimp Terminal, Series 70021, Male, 8.43mm Mating Length, 0.38µm Gold (Au) Plated, 24-22 AWG, Bag	16020115
SL Crimp Terminal, Series 70021, Male, 8.43mm Mating Length, 0.76µm Gold (Au) Plated, 24-22 AWG, Reel	16020116
SL Crimp Terminal, Series 70021, Male, 8.43mm Mating Length, 0.76µm Gold (Au) Plated, 24-22 AWG, Bag	16020117
SL Crimp Terminal, Series 71851, Female, with 0.38µm Selective Gold (Au) Plated Contact, 30-24 AWG, Reel	16020119
SL Crimp Terminal, Series 71851, Female, with 0.38µm Selective Gold (Au) Plated Contact, 30-24 AWG, Bag	16021109
SL Crimp Terminal, Series 71851, Female, with Tin (Sn) Plated Contact, 24-22 AWG, Reel	16021110
SL Crimp Terminal, Series 71851, Female, with 0.76µm Selective Gold (Au) Plated Contact, 24-22 AWG, Reel	16021111
SL Crimp Terminal, Series 71851, Female, with Tin (Sn) Plated Contact, 30-24 AWG, Reel	16021112
SL Crimp Terminal, Series 71851, Female, with 0.76µm Selective Gold (Au) Plated Contact, 30-24	16021113

Downloaded from Arrow.com.

AWG, Reel	
SL Crimp Terminal, Series 71851, Female, with Tin (Sn) Plated Contact, 24-22 AWG, Bag	16021114
SL Crimp Terminal, Series 71851, Female, with 0.76µm Selective Gold (Au) Plated Contact, 24-22 AWG, Bag	16021115
SL Crimp Terminal, Series 71851, Female, with Tin (Sn) Plated Contact, 30-24 AWG, Bag	16021116
SL Crimp Terminal, Series 71851, Female, with 0.76µm Selective Gold (Au) Plated Contact, 30-24 AWG, Bag	16021117
SL Crimp Terminal, Series 71851, Female, with Tin (Sn) Plated Contact, 36-32 AWG, Reel	16021118
SL Crimp Terminal, Series 71851, Female, with Tin (Sn) Plated Contact, 36-32 AWG, Bag	16021119
SL Crimp Terminal, Series 71851, Female, with 0.38µm Selective Gold (Au) Plated Contact, 36-32 AWG, Reel	16021120
SL Crimp Terminal, Series 71851, Female, with 0.38µm Selective Gold (Au) Plated Contact, 36-32 AWG, Bag	16021121
SL Crimp Terminal, Series 71851, Female, with 0.76µm Selective Gold (Au) Plated Contact, 36-32 AWG, Reel	16021122
SL Crimp Terminal, Series 71851, Female, with 0.76µm Selective Gold (Au) Plated Contact, 36-32 AWG, Bag	16021123
SL Crimp Terminal, Series 71851, Female, with 0.38µm Selective Gold (Au) Plated Contact, 24-22 AWG, Reel	16021124
SL Crimp Terminal, Series 71851,	16021125

Downloaded from Arrow.com.

Female, with 0.38µm Selective Gold (Au) Plated Contact, 24-22 AWG, Bag	
MicroClasp 2.00mm Pitch Crimp Terminal, Female, Tin (Sn) Plated, 26-22 AWG, Phosphor Bronze, Reel	561348000
MicroClasp 2.00mm Pitch Crimp Terminal, Female, Tin (Sn) Plated, 26-22 AWG, Phosphor Bronze, Bag	561348100
MicroClasp 2.00mm Pitch and MUO 2.5 Crimp Terminal, Female, Tin (Sn) Plated, 28-22 AWG, Copper Alloy, Reel	561349000
MicroClasp 2.00mm Pitch and MUO 2.5 Crimp Terminal, Female, Tin (Sn) Plated, 28-22 AWG, Copper Alloy, Bag	561349100
SL Crimp Terminal, Series 70021, Male, 8.43mm Mating Length, 0.38µm Gold (Au) Plated, 24-22 AWG, Reel	700210081
SL Crimp Terminal, Female, 30-24 AWG, with 0.38µm Selective Gold (Au) Plated Contact, Reel	700580082
SL Crimp Terminal, Female, 30-24 AWG, with 0.76µm Selective Gold (Au) Plated Contact, Reel	700580083
SL Crimp Terminal, Female, 24-22 AWG, with Tin (Sn) Plated Contact, Unplated Edges, Reel	700580086
SL Crimp Terminal, Female, 24-22 AWG, with 0.38µm Selective Gold (Au) Plated Contact, Reel	700580087
SL Crimp Terminal, Female, 24-22 AWG, with 0.76µm Selective Gold (Au) Plated Contact, Reel	700580088
SL Crimp Terminal, Female, 30-24 AWG, with 0.38µm Selective Gold (Au) Plated Contact, Bag	700580097
SL Crimp Terminal, Female, 24-22	700580103

Downloaded from Arrow.com.

AWG, with 0.38µm Selective Gold (Au) Plated Contact, Bag	
SL Crimp Terminal, Female, 30-24 AWG, with Tin (Sn) Plated Contact, Reel	700581069
SL Crimp Terminal, Series 70058, Female, 24-22 AWG, with Tin (Sn) Plated Contact, Unplated Edges, Reel	700584086

Downloaded from Arrow.com.