



Part Number : 22051042

Series Number : 5046

Product Category : PCB Headers and Receptacles

Product Description : Mini-Latch / KK Wire-to-Board Header, Right-Angle, with Friction Ramp, 4 Circuits, Tin (Sn) Plating, Natural

Status : New Business Not Supported

Engineering Number : 5046-04A

Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	New Business Not Supported
--------	----------------------------

Category	PCB Headers and Receptacles
Series	5046
Description	Mini-Latch / KK Wire-to-Board Header, Right-Angle, with Friction Ramp, 4 Circuits, Tin (Sn) Plating, Natural
Application	Signal, Wire-to-Board
Component Type	PCB Header
Product Family	Mini-Latch Wire-to-Board / Wire-to-Wire Connector System
Product Name	KK,Mini-Latch
UPC	800753591448

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	250V

Physical

Breakaway	No
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon

Net Weight	498.400/mg
Number of Rows	1
Orientation	Right Angle
Packaging Type	Bag
PC Tail Length	3.40mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	2.50mm
Pitch - Termination Interface	2.50mm
Plating min - Mating	5.080µm
Plating min - Termination	5.080µm
Polarized to PCB	No
Shrouded	Partial
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole

This document was generated on May 05, 2024