**Part Number :** 1201080030
**Product Description :** Micro-Change (M12) Double-Ended Cordset, 4 Poles, D-Coded, Male (Straight) to Male (Straight), 24 AWG, PVC Cable, 60.0m (196.85') Length
**Series Number :** 120108
**Status :** Active
**Product Category :** Industrial Cable Assemblies
**Engineering Part Number :** E11A06002M600



## Documents and Resources

### Drawings

1201080030_sd.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | Not Relevant |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Contains Lead; bis(2-ethylhexyl) tetrabromophthalate covering any of the individual isomers and/or combinations thereof per D(2025)4165-DC (25 June 2025) |
| EU RoHS | Compliant with Exemption 6(c) per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

Downloaded from Arrow.com.

- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Industrial Cable Assemblies |
| Series | 120108 |
| Description | Micro-Change (M12) Double-Ended Cordset, 4 Poles, D-Coded, Male (Straight) to Male (Straight), 24 AWG, PVC Cable, 60.0m (196.85') Length |
| IP Rating | IP67 |
| Performance Category | 5e |
| Product Name | Micro-Change (M12) |
| Type | Double Ended |
| UPC | 78678889595 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 1.5A |
| Voltage - Maximum | 125V |

### Physical

| | |
|---|---|
| Cable Diameter | 6.35mm (.250") |
| Cable Length | 60.0m (196.85') |
| Color - Cable Jacket | Blue Green |
| Connector End A | Micro-Change (M12) |
| Connector End B | Micro-Change (M12) |
| Coupling Style | Threaded |

Downloaded from Arrow.com.

| | |
|---|---|
| Gender | Male-Male |
| Keyway | D-Coded |
| LED Indicator | None |
| Material - Cable Jacket | PVC |
| Material - Connector Body | TPU |
| Material - Contact | Copper Alloy |
| Material - Coupling Nut | Nickel-plated Brass |
| Material - O-Ring | Fluoro-elastomer |
| Material - Plating Mating | Gold |
| Net Weight | 3254.000/g |
| Orientation | Straight to Straight |
| Poles | 4 |
| Temperature Range - Operating | -25° to +75°C |
| Wire/Cable Type | Unshielded-Stranded |
| Wire Size (AWG) | 24 |



Downloaded from Arrow.com.