



**Part Number :** [1204061046](#)  
**Product Description :** Ultra-Lock 2.0 (M12) Receptacle to RJ-45 Double-Ended Cordset, 4 Poles, D-Coded, Female (Straight) to RJ-45 Male (Straight), EtherNet Cat5e TPU Cable, Teal, 0.50m Length  
**Series Number :** 120406  
**Status :** Active  
**Product Category :** Circular Industrial Cordsets  
**Engineering Number :** ERYPAU7016M005



## Documents & Resources

**Drawings**  
[1204061046\\_sd.pdf](#)

## Product Environment Compliance

### Compliance

|                    |                                                                                       |
|--------------------|---------------------------------------------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                                                          |
| China RoHS         |  |
| EU ELV             | Not Relevant                                                                          |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21                                                       |
| REACH SVHC         | Contains Lead; Lead monoxide per D(2023)3788-DC (14 Jun 2023)                         |
| EU RoHS            | Compliant with Exemption 6(c) per EU 2015/863                                         |

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

## Part Details

### General

|                      |                                                                                                                                                                           |
|----------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Status               | Active                                                                                                                                                                    |
| Category             | Circular Industrial Cordsets                                                                                                                                              |
| Series               | 120406                                                                                                                                                                    |
| Description          | Ultra-Lock 2.0 (M12) Receptacle to RJ-45 Double-Ended Cordset, 4 Poles, D-Coded, Female (Straight) to RJ-45 Male (Straight), EtherNet Cat5e TPU Cable, Teal, 0.50m Length |
| IP Rating            | IP67, IP20                                                                                                                                                                |
| Performance Category | 5e                                                                                                                                                                        |
| Product Name         | Ultra-Lock 2.0 (M12),Industrial Ethernet                                                                                                                                  |
| Protocol             | EtherNet                                                                                                                                                                  |
| Type                 | Double Ended                                                                                                                                                              |
| UPC                  | 196823153778                                                                                                                                                              |

### Agency

|    |         |
|----|---------|
| UL | E361772 |
|----|---------|

### Electrical

|                               |                |
|-------------------------------|----------------|
| Current - Maximum per Contact | 1.5A           |
| Voltage - Maximum             | 30V AC, 42V DC |

### Physical

|                      |                      |
|----------------------|----------------------|
| Cable Diameter       | 6.50mm (.256")       |
| Cable Length         | 0.50m (1.64')        |
| Color - Cable Jacket | Teal                 |
| Connector End A      | Ultra-Lock 2.0 (M12) |
| Connector End B      | RJ-45 (standard)     |
| Coupling Style       | Push to Lock         |
| Gender               | Female-Male          |

|                               |                      |
|-------------------------------|----------------------|
| Keyway                        | D-Coded              |
| LED Indicator                 | None                 |
| Material - Cable Jacket       | TPU                  |
| Material - Connector Body     | TPU                  |
| Material - Contact            | Bronze               |
| Material - Coupling Nut       | Brass                |
| Material - O-Ring             | FPM   Nitrile Rubber |
| Material - Plating Mating     | Gold                 |
| Net Weight                    | 188.016/g            |
| Orientation                   | Straight to Straight |
| Poles                         | 4                    |
| Temperature Range - Operating | -40° to +85°C        |
| Wire/Cable Type               | UL 21215             |
| Wire Size (AWG)               | 24                   |

---

This document was generated on Apr 20, 2025