



Color:  white

Technical data	
Suitable	for cable diameter 5 ... 12 mm
Marking method	Thermal transfer
Marking	plain
Delivery form	Roll
Delivery form configuration	1,000 pcs/reel
Printing device	Smart Printer (thermal transfer printer)

Physical data	
Depth	0.12 mm
Marking surface	13 x 22 mm

Mechanical data	
Mounting type	Wrapping
Smear resistance	in conjunction with 258-5014 Ink Ribbon

Material data	
Color	white
Material	Polyvinyl chloride
UV resistance	EN 60068-2-5:2010 Procedure B
Adhesive information	Acrylic; permanent
Halogen-free	Yes
Weight	181 g
Fire load	0 MJ



Environmental requirements	
Ambient temperature (storage)	+10 ... +22 °C
Ambient temperature (operation)	-30 ... +120 °C
Relative humidity	40 ... 50 %

Commercial data	
Product Group	2 (Terminal Block Accessories)
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	DE
GTIN	4050821656869
Customs tariff number	39191080888

Product classification	
UNSPSC	55121612
eCl@ss 10.0	27-40-04-01
eCl@ss 9.0	27-40-06-29
ETIM 9.0	EC001530
ETIM 8.0	EC001530
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant, No Exemption

Downloads

Environmental Product Compliance

Compliance Search	
Environmental Product Compliance 211-856	

Documentation

Operating Instructions			
211-856 Information on printing material	1	pdf	
	28.08.2020	1316.17 KB	

Installation Notes

Marking



- Remove the printed label from the sheet or reel.
- Wrap the label around the conductor or cable.
- The transparent laminate protects the marking.

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: [www.wago.com](http://www.wago.com)