




- NOTES:
1. PARTS TO BE BULK PACKED.
 2. ASSEMBLE CONTACTS INTO CONNECTOR AFTER CRIMPING ONTO WIRES.
 3. ALL DIMENSIONS ARE REFERENCE ONLY EXCEPT WHERE NOTED WITH TOLERANCE. DIMENSIONS IN BRACKETS [] ARE METRIC.




CONTACT
INSERTION VIEW




ASSEMBLED VIEW




FACE VIEW
W5280-12SG-3XX




CABLE IN-LINE INSERT, FEMALE
MAT'L: UV THERMOPLASTIC,
BLACK




#20 SOCKET CONTACTS
CRIMP,
GOLD PLATED




GROMMET,
MAT'L: RUBBER,
BLACK
FOR CABLE O.D.
SEE TABLE




SLEEVE
MAT'L: THERMOPLASTIC,
BLACK




BACKSHELL
MAT'L: UV THERMOPLASTIC,
BLACK




WIRE VIEW
12-position



FACE VIEW
W5280-10SG-3XX



FACE VIEW
W5280-11SG-3XX



CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: _____

DATE: _____

A		PAK	08/20/19	DRAWING CREATED & RELEASED PER DOR 10-2523JS-1					
REV.		INIT.	DATE	DESCRIPTION					
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION". UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.				ORIG. DRAWN BY:		DATE:			
				PAK		09/29/14			
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS. UNLESS OTHERWISE SPECIFIED TOLERANCES: 3 PLACE DECIMALS ±.005 ANGLES ±1° FRACTIONS ±1/16				CHECKED BY:		601 E. WILDWOOD VILLA PARK, IL 60181			
▷ = CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXXX				APPROVED BY:		TITLE: CABLE TO CABLE CONNECTOR KIT #20 SOCKET CONTACTS (CRIMP)			
						MULTI-CON-X, E-KEY, WEATHER RESISTANT			
SCALE		SIZE		SHEET		CUSTOMER: STANDARD PRODUCT			
NTS		B		1 OF 1					
FILE:		W5280-1XSG-3XX		DIRECTORY:		PART NUMBER:		W5280-1XSG-3XX	
				SLW				REV A	

KIT PART NO.	GROMMET SIZE TO FIT CABLE O.D.
W5280-1XSG-324	0.24 - 0.27 [6.1-6.8mm]
W5280-1XSG-328	0.28 - 0.29 [7.1-7.4mm]
W5280-1XSG-330	0.30 - 0.32 [7.6-8.1mm]
W5280-1XSG-3DC	0.12-0.17-0.24 [3.0-4.3-6.1mm]

NO. OF CONTACTS

KIT P/N	NO. OF CONTACTS
W5280-10SG-3XX	(10) - #20
W5280-11SG-3XX	(11) - #20
W5280-12SG-3XX	(12) - #20
W5280-1XSG-3XX	

GROMMET SIZE
SEE P/N LIST

NO. OF CONTACTS