



Part Number : [1000631600](#)

Product Description : MLX 600 Coaxial Cable,
Double Shield, Low Loss, 5 AWG

Series Number : 100063

Status : Active

Product Category : Coaxial Cable



Documents and Resources

Drawings

[1000631600_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771- DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Coaxial Cable
Series	100063
Description	MLX 600 Coaxial Cable, Double Shield, Low Loss, 5 AWG
Product Name	MLX Coaxial Cable
UPC	198282536284

Electrical

Dielectric Constant	1.32
Impedance	50Ω
Inner Conductor DC Resistance	.53 Ohms/1000 ft
Max Cut Off Frequency	10.3 GHz
Nominal Capacitance	23.4 pF/ft
Nominal Inductance	.058 uH/ft
Outer Conductor DC Resistance	1.2 Ohms/1000 ft
Shielding Effectiveness	90 dB
Velocity of Propagation	85%

Physical

Color - Cable Jacket	Black
First Shield	Aluminum Tape
Flat Plate Crush	60 lbs/in
Insulation	Foam Polyethylene
Material - Outer Jacket	Polyethylene
Minimum Dynamic Bend Radius	6.00" (152.40mm)
Minimum Static Bend Radius	1.50" (38.10mm)
Net Weight	62.270/g
Outer Diameter	.590" (14.99mm)
Second Shield	Tinned Copper Braid

Signal Conductor	Solid Copper Clad Aluminum
Signal Conductor AWG	5
Temperature Range - Operating	-40° to +85°C
Temperature Range - Storage	-70° to +85°C
Tensile Strength	350 lbs
Weight	.137 lbs/ft

This document was generated on May 09, 2026