




A



B



C



D

NOTES:

## MATERIAL

1. Insulator Material: PBT+30%G.F(UL94V-0), Black

2. Contact Material: Brass

3. Contact Plating: Gold Flash or Tin plated

## ELECTRICAL

1. Current Rating: 3.0Amps/contact max

2. Withstand Voltage: 1000V AC/minute

3. Contact Resistance: 20mΩ/contact max

4. Insulation Resistance: 1000MΩ min at Voltage=100V

## ENVIRONMENTAL

1. Operation Temperature: -55°C to +105°C (Gold plated)  
-40°C to +105°C (Tin plated)

2. Mechanical life cycle: min.200

Packing: Tray

Order code: A-BL254-EG-xxx D

Contact plating

G: Gold flash

Z: Tin plated

**RoHS compliant**  
 Unit: mm

Scale	Free						Date	Name	Customer-No.	G
TOLERANCE							Drawn	18.09.2000	Hellwig	
X.	±0.50									
X.X	±0.30	(4)	Add Tin plating	07.05.2013	Amy	Approved	07.05.2013	Amy	ASSMANN WSW-No.	H
X.XX	±0.20	(3)	Update	27.09.2012	Amy				A-BL254-EG- xxx D	
X.XXX	±0.10	(2)	Modify drawing	27.07.2009	Dean				Drawing-No.	H
DIM	TOL	(1)	Drawn	18.09.2000	Hellwig				ASS 1034A CO	
Angle	±5°	Id.	Modification	Date	Name				rev04	
								Replace	SHEET	

**ASSMANN**  
 WSW components