




STANDARD GRAPHICS MODULES

G64128X09..... OUTLINE DIMENSION AND BLOCK DIAGRAM



NOTES:

- 1.VDD = 3.0V (TYP); 3.6V (MAX)
- 3.IDD = 900uA (TYP)
- 4.DUTY CYCLE = 1/64
- 5.BIAS = 1/9
- 6.CONTROLLER = S1D10605D
- 7.CONNECTOR = HEATSEAL/FFC
- 8.UNMARKED TOLERANCES = ±0.30mm

PIN ASSIGNMENT

PIN	1	2	3	4	5	6	7	8	9
SYMBOL	V _{SS}	V _{DD}	V _O	RES	CS	RS	R/W	E	DB0

PIN	10	11	12	13	14	15	16	17	18
SYMBOL	DB1	DB2	DB3	DB4	DB5	DB6	DB7	A	K

BACKLIGHT OPTION

LED COLOR	OPTION	VOLTAGE(V)	FORWARD CURRENT(mA)		
			MIN	TYP	MAX
YELLOW GREEN	YES	4.1	-	60	120
WHITE	YES	4.0	-	60	80
BLUE	NO	-	-	-	-

CCT reserves the right to vary or make changes to the specifications of the module in this brochure at any time without prior notice. CCT further assumes no responsibility for its use, nor for any infringements of patents, pending applications or the rights of thirds parties as a result of its use.