



D SUBMINIATURE CONNECTOR KH SERIES

Right angle through-hole socket

RIGHT ANGLE THROUGH-HOLE SOCKET



(with hexagonal lock screw blocks)



(without lock screw blocks, but with grounding adapters having a No.4-40UNC inch thread)

Features

- The depth is trimmed to 13.0 mm, reducing the surface mounting area by 20% compared with our JK series subminiature connectors.

* RoHS2 compliance

* Refer to "General Instruction and Notice when using Terminals and Connectors" at the end of this catalog.

* Contact JST for details.



KH series	JK series

Standards

Recognized E60389

Certified LR20812

Right angle through-hole socket



H: Height of the lock screw block (for Types A, B & J)

Circuits	Model No.		Q'ty/ box
	Gold-plated (flash) receptacle	Gold-plated (0.76 micron) receptacle	
15	KHEY-15S-1A**	KHEY-15S-1A**14	100


RoHS2 compliance This product displays (LF)(SN) A on a label.

Note: ** shows the location where a two-digit code (see the table below for codes) should be entered. For example, if a 15-circuit gold-plated (flash) socket with hexagonal lock screw blocks having a No.4-40UNC inch thread and with grounding adapters having a spring lock device is required, specify the model number as KHEY-15S-1A3A.

Type A



With hexagonal lock screw blocks (H:6.3 mm) having a No.4-40UNC inch thread



With grounding adapters with a spring lock device



3A

D SUBMINIATURE CONNECTOR KH SERIES

Specifications

Materials

Part name	Material and Finish
Contact	Phosphor bronze, nickel-undercoated, Mating part: gold-plated Solder tail: tin-plated (reflow treatment)
Insulator	Glass-filled PBT, UL94-0, black
Shell	Steel, copper-undercoated, nickel-plated
Grounding adapter with spring lock device	Brass, nickel-undercoated, tin/copper alloy-plated

Characteristics


Current rating	1.0 A AC/DC
Voltage rating	250 V AC/DC
Temperature range	-40°C to +85°C (including temperature rise in applying electrical current)
Contact resistance	Initial value/ 15 mΩ max. After environmental tests/ 30 mΩ max.
Insulation resistance	5,000 MΩ min.
Withstanding voltage	1,000 VAC/minute
Applicable PC board thickness	1.6 mm

*Contact JST for details.

Model number identification

K H E	Y	- 15	S	- 1A	3	A	14
• Series name	• Shell size: E	• Wire connection type: Y ... Right angle through-hole type	• Number of circuits: 15	• Connector type: S ... Socket	• Connector construction/dimensions: Standard KH series right angle through-hole type	• Types of grounding adapter: 3 ... With grounding adapters having a spring lock device	• Type of lock screw block: A ... With hexagonal lock screw blocks having a No. 4-40UNC inch thread B ... With hexagonal lock screw blocks having an M2.6 thread F ... Without lock screw blocks, but with grounding adapters having a No. 4-40UNC inch thread G ... Without lock screw blocks, but with grounding adapters having an M2.6 thread H ... Without lock screw blocks, but with grounding adapters having an M3 thread J ... With hexagonal lock screw blocks having an M3 thread
• Finish of mating part Blank ... Gold-plated (flash)	12 ... 0.2 micron gold-plated	13 ... 0.4 micron gold-plated	14 ... 0.76 micron gold-plated				

PC board layout (viewed from component side) and Panel layout



Note: 1. Tolerances are non-cumulative: ± 0.05 mm for all centers.
2. Hole dimensions differ according to the type of PC board and piercing method.
The dimensions above should serve as a guideline. Contact JST for details.

Type B	Type D	Type F	Type G	Type H
With hexagonal lock screw blocks (H:6.3 mm) having an M2.6 thread	Without lock screw blocks F, G, H: Grounding adapters have a thread (*1) for securing separately-purchased lock screw blocks (*2)			With hexagonal lock screw blocks (H:6.3 mm) having an M3 thread
3B	3F	3G	3H	3J



D SUBMINIATURE CONNECTOR J·JH·JK&KH SERIES


Accessories/Lock screw block

A variety of accessories are available for the D subminiature connectors.


LOCK SCREW BLOCK




Hexagonal lock screw block
(inch thread: No.4-40UNC)



No.4-40UNC



No.4-40UNC



No.4-40UNC

Type A

Type B


Hexagonal lock screw & spring washer are integrated

Applicable series	J series right angle through-hole type JK series straight through-hole type	JK series right angle through-hole type	J series straight through-hole type	JH series right angle through-hole type KH series right angle through-hole type	Dimension H (mm)	Type	Attachment	Q'ty/box
Dimension / Model No.	13.1	15.0	10.0	11.8				
Dimension L (mm)	13.1	15.0	10.0	11.8				
Model No.	JFS-4S-C1N	KFS-4S-C1N	—	—	5.5	A	Spring washer .. 1 pc. Nut 1 pc.	2,000
	JFS-4S-B1W	KFS-4S-B1W	SFS-4S-B1W	HFS-4S-B1W	4.8		Spring washer .. 1 pc.	
	JFS-4S-C1W	KFS-4S-C1W	—	—	5.5	B	—	
	JFS-4S-B1WM	KFS-4S-B1WM	SFS-4S-B1WM	HFS-4S-B1WM	4.8		—	
	JFS-4S-C1WM	KFS-4S-C1WM	SFS-4S-C1WM	HFS-4S-C1WM	5.5		—	


RoHS2 compliance




Hexagonal lock screw block
(metric thread: M3)



M3



M3



M3

Type A

Type B

Hexagonal lock screw & spring washer are integrated


Applicable series	JK series right angle through-hole type	J series straight through-hole type	JH series right angle through-hole type KH series right angle through-hole type	Dimension H (mm)	Type	Attachment	Q'ty/box
Dimension/ Model No.	15.0	10.0	11.8				
Dimension L (mm)	15.0	10.0	11.8				
Model No.	—	SFS-3S-B1W	—	4.8	A	Spring washer .. 1 pc.	2,000
	—	SFS-3S-C1W	HFS-3S-C1W	5.5		Spring washer .. 1 pc.	
	—	—	—	4.8	B	—	
	KFS-3S-C1WM	—	—	5.5		—	

RoHS2 compliance

D SUBMINIATURE CONNECTOR J·JH·JK&KH SERIES



Hexagonal lock screw block
(metric thread: M2.6)




Type A
Type B
Hexagonal lock screw & spring washer are integrated

Applicable series	J series right angle through-hole type	JK series right angle through-hole type	J series straight through-hole type	JH series right angle through-hole type	Dimension H (mm)	Type	Attachment	Q'ty/box
Dimension/Model No.	JK series straight through-hole type							
Dimension L (mm)	13.1	15.0	10.0	11.8				
Model No.	JFS-2.6S-C1N	—	—	—	5.5	A	Spring washer .. 1 pc. Nut 1 pc.	2,000
	JFS-2.6S-B1W	KFS-2.6S-B1W	SFS-2.6S-B1W	—	4.8		Spring washer .. 1 pc.	
	JFS-2.6S-B1WM	—	SFS-2.6S-B1WM	HFS-2.6S-B1WM	4.8	B	—	
	JFS-2.6S-C1WM	—	SFS-2.6S-C1WM	—	5.5		—	

RoHS2 compliance




Rectangular lock screw block
(metric thread: M2.6)



Model No.	Attachment	Q'ty/box
JFS-2.6R-N	Spring washer 1 pc. Set screw 1 pc.	1,000

RoHS2 compliance


D SUBMINIATURE CONNECTOR J·JH·JK&KH SERIES





Application examples of hexagonal lock screw blocks

- The resulting total dimension from the connector flange to the top of the hexagonal lock screw block must be 6.2 mm after assembly.
- The D subminiature connector can be installed on the Panel by simply tightening the hexagonal lock screw block together with grounding adapter, which has an identical thread to that of the F, G, and H types.


DUST COVER (for receptacles)



Type A



Type B



Type	Circuits		Model No.	Q'ty/box
	J series	JK series		
A	9	15	J-DCES	1,000
B			J-DCES-1	
Material				
PA, UL94V-0, black				

RoHS2 compliance

EXTRACTION TOOL



With this tool, contacts (connected to wires by crimping) can be easily removed if they are improperly inserted into plug and receptacle housings.

Applicable Connector		Model No.
J series		DEJ-0.3
JK series	Plug	KEJ-0.7
	Receptacle	KEJ-0.4