



APC Smart-UPS On-Line, 3kVA, Rackmount 2U, 230V, 8x C13+2x C19 IEC outlets, Network Card, Extended runtime, W/ rail kit

SRT3000RMXLI-NC

#### **Overview**

Presentation	High density, double-conversion on-line power protection with scalable runtime.
Lead time	Usually in Stock

Main	
Main Input Voltage	230 V
Product or component type	Uninterruptible power supply (UPS)
Other Input Voltage	220 V 240 V
Main Output Voltage	230 V
Other Output Voltage	220 V 240 V
Rated power in W	2700 W
Rated power in VA	3000 VA
Input Connection Type	BS1363A British IEC 60320 C20 Schuko CEE 7 / EU1-16P
output connection type	8 IEC 60320 C13 2 IEC Jumpers 2 IEC 60320 C19
Number of rack unit	2U
Cable length	2.4 m
Number of cables	1
Provided equipment	CD with software Documentation CD Installation guide Network management card Rack mounting brackets Rack mounting support rails USB cable Warranty card
Range of product	Smart-UPS On-Line

### **Batteries & Runtime**

Run Time	View Runtime Graph ☐
Efficiency	View Efficiency Graph ☐
Battery type	Lead-acid battery
Battery voltage	96 V
Extended runtime	1

Number of battery filled slots	1
Battery recharge time	3 h
Number of battery replacement quantity	1
Battery life	35 year(s)
Replacement battery	APCRBC152 ☐
Battery charger power	168 W rated

### General

Number of power module filled slots	0
Number of power module free slots	0
product web sub-family	High density
Redundant	No
UPS type	Double conversion online

# **Physical**

Colour	Black
Height	8.5 cm
Width	43.2 cm
Depth	63.5 cm
Product weight	31.3 kg
Mounting location	Front
Mounting preference	Lower
Mounting mode	Rack-mounted
Two post mountable	0
USB compatible	Yes
Mounting position	Horizontal

# Input

Input voltage limits	100275 V adjustable (half load)
Network frequency	4070 Hz auto-sensing

# Output

Bypass type	Internal bypass (automatic and manual)
Crest factor	3:1
Harmonic distortion	Less than 2 %
Maximum configurable power in VA	3000 VA
Maximum configurable power in W	2700 W
Wave type	Sine wave
Output frequency	50/60 Hz +/- 3 Hz sync to mains
Additional information	Configurable for 220 : 230 or 240 nominal output voltage

#### Conformance

Product certifications	CE EAC RCM VDE UK PSTI
Marking	CE Mark
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

#### **Environmental**

Acoustic level	55 dBA
Heat dissipation	703 Btu/h
Operating altitude	010000 ft
Ambient air temperature for operation	040 °C
Ambient air temperature for storage	-1545 °C
Storage altitude	0.000000000015240.0000000000 m
IP degree of protection	IP20
Relative humidity	095 % non-condensing
Storage Relative Humidity	095 % non-condensing

### **Communications & Management**

Emergency power off	Yes
Free slots	0
Preinstalled device	Network management card 3 with environmental monitoring
Alarm	Audible and visible alarms : prioritized by severity

### **Surge Protection and Filtering**

Surge energy rate 340 J

# **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	24.6 cm
Package 1 Width	87.1 cm
Package 1 Length	59.9 cm
Package 1 Weight	39.92 kg

### **Contractual warranty**

Warranty 3 years repair or replace (excluding battery) and 2 years for battery



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability >

∇ Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	4988
Environmental Disclosure	Product Environmental Profile

#### **Use Better**

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
SCIP Number	A64c500c-f72a-458b-8faa-8175a94429fe
Optimized Energy Efficiency	Energy efficient product

#### **Use Again**

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Removable battery	User replaceable
Take-back	Yes