


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1552210025](#)
Status: **Active**
Overview: [Flamar Standard Cables for Industrial Automation](#)
Description: Flamar Sensor Cable, WSOR Jacket, Braided Shielding Overall, 5 Circuits, 0.34mm² / 22 AWG, 6.10mm (.240") Diameter, 300.0m (984.25') Length, Black

Documents:
[Product Specification 1552200001-P1E \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Cable
Series	155221
Comments	3 reels of 100.0m each
Crimp Quality Equipment	Yes
Geographic Area	Global
Overview	Flamar Standard Cables for Industrial Automation
Product Literature Order No	987651-3992
Product Name	Flamar
UPC	889056464079
Physical	
Bending Radius - Minimum	> 7.5xOD
Cable Length	300.0m
Circuits (Loaded)	5
Color - Cable Jacket	Black
Insulation	TPE
Material - Outer Jacket	WSOR
Net Weight	0.010/g
Outer Jacket Diameter	6.10mm
Packaging Type	Reel
Temperature Range - Operating	-25°C to +80°C
Wire Size AWG	22
Wire Size mm²	0.34
Wire/Cable Type	Signal and Control, UL AWM 21215 / CSA
Electrical	
Current - Maximum per Contact	Contact Molex
Voltage - Maximum	600V
Material Info	
Engineering Number	BS1-5-3X100M
Reference - Drawing Numbers	
Product Specification	1552200001-P1E



Series image - Reference only

EU ELV
Not Reviewed

EU RoHS Not Reviewed REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed	China RoHS
---	-------------------

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[155221](#) Series

Use With
Nano-Change® (M8) [120091](#) , Micro-Change® (M12) [120071](#) , Ultra-Lock® (M12) [120085](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION