

REV. Status

REVISION –
11/14/95 TSREVISION A
ADDED RoHS
12/02/05 MPREVISION B
REV DC RES
WAS 90Ω ±20%
02/01/08 YSREVISION C
ADDED TEMP
RATING
4/29/15 MP

AUDIO COUPLING MINIATURE ENCAPSULATED TRANSFORMER DESIGNED TO OPERATE 25mW MAX IN PRIMARY AND REFLECT A PRIMARY SOURCE IMPEDANCE OF APPROXIMATELY 50KΩCT WITH 1KΩCT LOAD ON SECONDARY.


A. Electrical Specifications (@ 20 ° C)

1. Pri Source Impedance; 50KΩ CT
2. Sec Load Impedance; 1KΩ CT
3. Pri DC Current; 0 mA MAX
4. Operating Level; 25 mW MAX @ 300 Hz
5. Frequency Response (relative to 1 KHz);
±2.0 dB, @ 300 Hz to 100 KHz
6. Longitudinal Balance; 60 dB MIN @ 1 KHz
7. DC Resistance;
(1-3) 3800Ω ±20%
(4-6) 105Ω ±20%
8. Turns Ratio; (1-3) : (4-6) = 7.07 : 1 ±2%
9. Dielectric Strength;
500 Vrms 0.5 minute @ Pri – Sec

B. Marking; MET-03, TAMURA, Primary and Secondary Impedance, PM7-M, MICROTRAN, TF5S21ZZ, date code and country of origin


C. Operating Temperature: -20 to +85°C
Storage Temperature: -55 to +105°C

D. Schematic Diagram




MODEL NUMBER

MET-03



E. Mechanical Specifications



TOLERANCES (mm)

≤ 4 ± 0.2
4 ≤ 20 ± 0.3
20 ≤ 50 ± 0.4

PREPARED BY:

C. POPPE

ENGINEER:

MATHI P.

SAFETY ENGINEER

APPROVED:

M. PITCHAI

DRAWING CONTROL NO.

P-A1-11461

REV

C

MODEL DESCRIPTION

AUDIO COUPLING
MINIATURE ENCAPSULATED XFMR

MODEL SPECIFICATION

MET-03

CONTENTS OF THIS DRAWING ARE
SUBJECT TO CHANGE WITHOUT
PRIOR NOTICE

TAMURA CORPORATION OF AMERICA
1040 SOUTH ANDREASEN DRIVE, #100 ESCONDIDO, CA. 92029
(951) 699-1270 FAX 7607400536

DIM: mm[In] SCL: 2/1 SH: 1 OF 1

PROPRIETARY NOTICE: THIS DRAWING PRINT OR DOCUMENT AND SUBJECT MATTER DISCLOSED HEREIN ARE PROPRIETARY ITEMS TO WHICH TAMURA RETAINS THE EXCLUSIVE RIGHT OF DISSEMINATION, REPRODUCTION, MANUFACTURE AND SALE. THIS DRAWING, PRINT OR DOCUMENT IS SUBMITTED IN CONFIDENCE FOR CONSIDERATION BY THE RECIPIENT ALONE UNLESS PERMISSION FOR FURTHER DISCLOSURE IS EXPRESSLY GRANTED IN WRITING.